ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



STL360 1000W SUPER STEALTH 360 SENSOR BRONZE

RAB LIGHTING

Catalog Number	STL360
Manufacturer	RAB LIGHTING
Description	Outdoor Sensors Stealth 360 Sensor 1000W 120V Bronze
Weight per unit	1.5 (lbs/each)
Product Category	Lighting Sensors

Features

Wattage	1000

Descriptions

Description	1000W SUPER STEALTH 360 SENSOR BRONZE
Long Description	Outdoor Sensors Stealth 360 Sensor 1000W 120V Bronze
Product Type	Super Stealth 360 Senr 1000W 120V Bron
Special Features	NONFIXTURE
Extra Long Description	RAB STL360 SUPER STEALTH 360 SENR 1

Manufacturer Information

Brand	RAB Lighting Inc
	Rab Lighting
GTIN	00019813761206
Manufacturers Part Number	STL360
UPC	885360

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	SENSOR

Packaging

Carton	1
Package	6
Weight Per Each	1.5 (lbs/each)

Uses, Certifications, and Standards

Application	Outdoor
Mounting	CEILING
Standard	360 degrees detection

STL360



Super Stealth Sensor with Total 360 + 180 "Can't Miss" Coverage, Surge Protection, Scanning LEDs, Evening Timer and Color Matched Lens, universal CU4 cover plate included.

Color: Bronze

Weight: 1.5 lbs

Project:	Type:
Prepared By:	Date:

Technical Specifications

Compliance

UL Listed:
Suitable for wet locations

Electrical

Voltage:
120V AC 60Hz

Power Consumption:
1W

Surge Protection:
Withstands up to 6000 volts

Wall Switch Manual Override:
Two flip logic prevents activation by momentary power outages. Override resets to auto at dawn. No extra wiring needed.

RF Immunity:
Circuits fully shielded for maximum radio frequency immunity

Switching Capacity:
8 amps, 1000W incandescent @ 120 volts

Sensor Specifications

Time Adjustment:
5 seconds to 12 minutes

Wide Sensitivity Control:
Adjustable from 100% to 30%

Evening Timer:
Keeps lights on for 1-8 hours after dusk. Then sensor is motion activated until dawn.

Set it and forget it:
STL360's full coverage pattern reduces need for aiming and adjustment

Advanced Detection Logic:
Minimizes false triggers

Photoelectric Control:
Deactivates lights during daylight. Fully adjustable for 24 hour operation or custom applications.

Detection:
Senses 180° and 360° down for Total Detection

LED Characteristics

Scanning LEDs:
3 LEDs continually scan back-and-forth

Color Matched Lens:
Dark lens with bronze units, white lens with white units

Construction

Temperature Compensation:
Sensitivity adjusted automatically for consistent detection in hot and cold ambient temperatures

Mounting:
CU4 plate allows the sensor to be mounted under a soffit

Lens Masks:
Customized press apply lens mask included to reduce coverage easily


Other

Warranty:
10-year sensor warranty

Buy American Act Compliance:
RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice

Dimensions



Features

- Senses 180° out + 360° down for total detection
- Radio frequency immunity
- 6000 volt surge protection
- Quick test time
- Color matched vandal resistant
- 1000 Watt switching capacity
- Pre-wired and pre-assembled on CU4 universal EZ plate
- Protected manual override with auto reset
- Can be wired in parallel

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice