ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



# TEL224 22/4C PHONE CABLE

*SOUTHWIRE COMPANY*

| | |
|---|---|
| Catalog Number | TEL224 |
| Manufacturer | SOUTHWIRE COMPANY |
| Description | 22 AWG 4/C SOLID CU N/S CM/CL2 GY 500PB |
| Weight per unit | 0.0200 (lbs/ft) |
| Product Category | Wire |

## Descriptions

| | |
|---|---|
| Description | 22/4C PHONE CABLE |
| Long Description | 22 AWG 4/C SOLID CU N/S CM/CL2 GY 500PB |
| Product Type | Sy 22/4 Sol Cu N/S CM/CL2 Gy 500PB |
| Extra Long Description | SWC 962384509 SY 22/4 SOL CU N/S CM |

## Manufacturer Information

| | |
|---|---|
| Brand | Southwire |
| | Cables & Cords |
| GTIN | 00029892441005 |
| Manufacturers Part Number | 962384509 |
| UPC | 885800 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | ELECTRONIC CABLE |

## Packaging

| | |
|---|---|
| Carton | 1000 |
| Weight Per Each | 0.0200 (lbs/ft) |

# Burglar Alarm cable Solid and Stranded CM/CL2 Rated



96222 96238



51101 51112

Intertek

APPLICATIONS — Burglar alarm interconnect cables to comtrols systems, Class 2 Power Limited Circuit Cable and Communications Cable for General Purpose Applications

CONSTRUCTION

| | |
|---|---|
| A.) CONDUCTOR | 22 AWG solid or stranded Bare Copper |
| B.) INSULATION | Foam Polypropylene |
| C.) COLOR CODE | See table |
| D.) SHIELDING | Unshielded |
| E.) ASSEMBLY | This cable consists of insulated conductors with an overall extruded jacket. |
| F.) JACKET | Smooth, round, flexible PVC. Colors: White, Gray, Brown, Beige (Other colors available for minimum order) |

COMPLIANCE

| | |
|---|---|
| A.) FLAME TEST | UL 1685 (by UL) / CSA FT1 |
| B.) CABLE TYPE | UL Standard 13 and 444, NEC Articles 725 and 800, CM/CL2 |
| C.) VOLTAGE | 300 V RMS Max. |
| D.) TEMPERATURE | -20°C to 75°C |
| E.) SUITABLE USE: | General purpose low voltage and power-limited systems. Suitable for use in indoor use, circuits to NEC Article 725 and 800 |

FEATURES & OPTIONS: Available in 1000ft or 500 ft packages, reels, or pull-boxes where practicable.

| Stock # | DESCRIPTION | AWG | #COND | STRANDS | Rating | NOM. DIA. (Inches) | WEIGHT (Lb/Mft) | COLOR CODE |
|---|---|---|---|---|---|---|---|---|
| 96222 | 22/2 Conductors BC | 22 | 2 | Solid | CM | 0.102 | 7 | Red, Green |
| 96238 | 22/4 Conductors BC | 22 | 4 | Solid | CM | 0.117 | 12 | Blk, Red, Yel, Grn |
| 51101 | 22/2 Conductors BC | 22 | 2 | Stranded | CM | 0.11 | 9 | Blk, Red |
| 51112 | 22/4 Conductors BC | 22 | 4 | Stranded | CM | 0.126 | 13 | Blk, Red, Wht, Grn |


©2021 Southwire Company, LLC. All Rights Reserved.