ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



TSR3I8A ONE PIECE SURFACE RACEWAY, 1-3/4" X 8', PVC, IV

HELLERMANNTYTON

Catalog Number	TSR3I8A
Manufacturer	HELLERMANNTYTON
Description	HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate dif
Weight per unit	0.1712 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

Material	Polyvinyl Chloride (PVC)
Media	Yes

Dimensions and Weight

Height	1
Length	96
Width	1.75

Descriptions

Description	ONE PIECE SURFACE RACEWAY, 1-3/4" X 8', PVC, IV
Features	Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.
Long Description	HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate dif
Product Type	TSR3-8A PVC Iv 160.0 FT/CTN
Short Description	TSR3-8A PVC IV 160.0 FT
Special Features	1-3/4" One Piece Surface Raceway, PVC, 8 ft Long, Ivory, 160/Carton
Extra Long Description	TYN TSR3I-8A TSR3-8A PVC IV 160.0 F

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Hellermanntyton
GTIN	04031026724164
Manufacturers Part Number	TSR3I-8A
UPC	675301

Taxonomies, Classifications, and Categories

Category Description	Wire/Plug Strips, Surf Raceways, Power Pole, Walkerduct, & Plugmolds
Type	TSR3-8A

Packaging

Carton	160
Weight Per Each	0.1712 (lbs/each)

Specification Sheet

Part Number: TSR3I-8A

Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.

PVC construction is lightweight, durable and more affordable than metallic raceway systems.

Flexible hinge is designed to reduce stress cracking and discoloration from repeated opening and closing.

Foam tape backing with rubber based adhesive conforms to any flat surface to assist with temporary positioning and mounting.

Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.

Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.



One Piece Surface Raceway, 1-3/4", 8.0 ft Long, PVC, Ivory, 160ft/Carton

Article Number	250-03801
Type	TSR3-8A
Color	Ivory (IV)
Quantity Per	carton

Product Description	HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one-piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations.
Short Description	One Piece Surface Raceway, 1-3/4", 8.0 ft Long, PVC, Ivory, 160ft/Carton
Global Part Name	TSR3-8A-PVC-BGE
Length L (Imperial)	8.0
Length L (Metric)	2.44
Width W (Imperial)	1.75
Width W (Metric)	44.45
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC

Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	160.0
Package Quantity (Metric)	48.80
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.