Specifications

Eaton UT4R1121BCH

Catalog Number: UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

Product Name
Eaton meter socket

Catalog Number
UT4R1121BCH

UPC
782116094639

Product Length/Depth
4.5 in

Product Height
14.13 in

Product Width
40.63 in

Product Weight
40 lb

Warranty
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications
UL Listed

Powering Business Worldwide

Product specifications

Type

Multiple position commercial or residential service

Amperage Rating

100A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power
ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)
SC : South Carolina Electric and Gas (SCE&G)
AR : Entergy
LA : Entergy
MS : Entergy
TX : Entergy

Line

#6-250 kcmil

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Number of sockets

4

Resources

Drawings

Dimensional Drawing - SKT/4 GANG 100A 1P HO

Specifications and datasheets

Metering Equipment - Utilities Servicing Illinois, Iowa, Kansas, Missouri, Oklahoma and Wisconsin

Eaton Specification Sheet - UT4R1121BCH

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia