



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 108612CHC Encl HNGD CVR Encl *Cooper B-Line/Cable Tray*

Catalog Number	108612CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 10" Height, 6" Length, 8" Width, Nema 12, Hinged Cover, 12CHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	7.8 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

dimensions	6.0000 IN X 8.0000 IN X 10.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

### Dimensions and Weight

Size	8.00 In Width X 6.00 In Depth X 10.00 In Height
------	---

### Descriptions

Description	ENCL HNGD CVR ENCL
extra long description	B-LINE 1086-12CHC TYPE 12 JIC CONTI
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 10" height, 6" length, 8" width, NEMA 12, Hinged cover, 12CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 Jic Continuous Hinge CVR Enc, 10X8X6
Special Features	Cont. piano hinge, panel mount, plated door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051700183
Manufacturers Part Number	1086-12CHC
UPC	782051700183

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	7.833

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Automation and Monitoring Commercial / Institutional Buildings / Structures - Power Distribution and Controls Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Lighting and Lighting Controls Ind Facilities & Factories - Industrial Facilities/Factories - Other Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Ind Facilities & Factories - Facility: Power Distribution and Control Ind Facili
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	UL 508A, CSA C22.2., NEMA