ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



WP3460WH CAT 6 RJ45 T568 A/B CONN WH (M20)

PASS & SEYMOUR/LEGRAND

Catalog Number	WP3460WH
Manufacturer	PASS & SEYMOUR/LEGRAND
Description	Keystone Connector, Snap-In Connection, White, 1.28 in Length, 0.64 in Width, 0.87 in Height, 0.04 lb/EA
Weight per unit	0.0369 (lbs/each)
Product Category	Fiber-Optic Connectors

Features

Cable Type	CAT6

Descriptions

Description	CAT 6 RJ45 T568 A/B CONN WH (M20)
Features	This high-quality Cat 6 RJ45 Keystone Connector in blue is designed for use in all Keystone Wall Plates. The standard RCA front jack connects to Cat5, Cat5e, or Cat6 cables terminated with RJ-45 plugs. The vertical design simplifies punchdown termination, while rear retention caps ensure secure wire connections. It meets Category 6 standards described in TIA/EIA-568-B.2.
Long Description	This high-quality Cat 6 RJ45 Keystone Connector in blue is designed for use in all Keystone Wall Plates. The standard RCA front jack connects to Cat5, Cat5e, or Cat6 cables terminated with RJ-45 plugs. The vertical design simplifies punchdown termination, while rear retention caps ensure secure wire connections. It meets Category 6 standards described in TIA/EIA-568-B.2.
Product Type	Cat 6 RJ45 T568 A/B CNCTR WH (M20)
Extra Long Description	PAS WP3460WH CAT 6 RJ45 T568 A/B CN

Manufacturer Information

Brand	LEGRAND-ON-Q
	LEGRAND-PASS & SEYMOUR
GTIN	00804428024361
Manufacturers Part Number	WP3460WH
UPC	785007

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories

Packaging

Carton	20
Package	120
Weight Per Each	0.0369 (lbs/each)

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Environmental Conditions	0 to 93% (relative humidity, non-condensing)
Nema Rating	0.63 x 0.87 x 1.26
Standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0

On-Q
Cat 6 RJ45 Keystone Connector
Part No. WP3460WH



This high-quality Cat 6 RJ45 Keystone Connector in white is designed for use in all Keystone Wall Plates. The standard RCA front jack connects to Cat5, Cat5e, or Cat6 cables terminated with RJ-45 plugs. The vertical design makes punchdown termination easy, while rear retention caps ensure secure wire connections. It meets Category 6 standards described in TIA/EIA-568-B.2.

Features & Benefits

- Standard RCA front jack
- Connects to Cat5, Cat5e, or Cat6 cables terminated with RJ-45 plugs Rear retention caps ensure secure wire termination
- Vertical design for easy punchdown termination
- T658A and T568B wiring labels included
- Meets Category 6 described in TIA/EIA-568-B.2
- Insertion and extraction life is 750 Cycles Min
- Jack housing is high-impact, flame resistant plastic, UL 94V-0
- Spring wire is phosphor bronze alloy plated with 50 micro-inch of gold over 100 micro-inches of nickel

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428024361	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential	Standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0

Dimensions

Product Width US	0.64 in	Product Height US	0.87 in
Product Length US	1.28 in		

Technical Information

Termination Style	Punchdown	Cable Type	Cat6
Environmental Conditions	0 to 93% (relative humidity, non-condensing)		