ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



WPLED10 *DISCONTINUED* LED WALLPACK 10W BLACK FINISH

RAB LIGHTING

Catalog Number	WPLED10
Manufacturer	RAB LIGHTING
Description	LED Wallpack, Die-Cast Aluminum, 5000 K, 547 lm Brightness (Lumens), 50 Hz;60 Hz, Bronze, 5 in Length, 2-1/8 in Width, 4-3/4 in Height, Black, 100000 h Average Life, 5 yr Warranty, 3.3 lb
Weight per unit	4.1 (lbs/each)
Product Category	Led Wallpacks

Features

Voltage Rating	120/277
Wattage	10
Lumens	1208

Descriptions

Description	*DISCONTINUED* LED WALLPACK 10W BLACK FINISH
Long Description	Wall Packs 1333 Lumens Wpled 10W Bronze
Product Type	Wallpk 10W Cool Junction Box
Special Features	LED
Extra Long Description	RAB WPLED10 WALLPK 10W COOL JUNCTIO

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00019813018232
UPC	885360

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Wallpack

Packaging

Carton	1
Weight Per Each	4.1 (lbs/each)

WPLED10

RAB Outdoor



LED 10W & 13 Wallpacks. Patent Pending thermal management system. 100,000 hour L70 lifespan. 5-year, no-compromise warranty.

Color: Bronze

Weight: 3.3 lbs

Project:	Type:
Prepared By:	Date:

Driver Info

Type:	Constant Current
120V:	0.1A
208V:	0.07A
240V:	0.06A
277V:	0.05A
Input Watts:	12W
Efficiency:	81%

LED Info

Watts:	10W
Color Temp:	5000K (Cool)
Color Accuracy:	73 CRI
L70 Lifespan:	100,000
Lumens:	1,208
Efficacy:	97 LPW

Technical Specifications

Listings

UL Listing:

Suitable for Wet Locations as a Downlight. Suitable for Damp Locations as an Uplight. Wall Mount only. Suitable for Mounting within 4ft. of ground.

IESNA LM-79 & IESNA LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

Electrical

THD:

10.8% at 120V, 13.8% at 277V

Power Factor:

98.5% at 120V, 92.1% at 277V

Driver:

Multi-chip 10W high output long life LED Driver Constant Current, Class II, 120V-240V, 50/60/ Hz, 350mA

LED Characteristics

Lifespan:

100,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

Color Consistency:

7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

Color Stability:

LED color temperature is warrantied to shift no more than 200K in CCT over a 5 year period

Color Uniformity:

RAB's of CCT (Correlated color temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

Lumen Maintenance:

The LED will deliver 70% of its initial lumens at 100,000 hours of operation

Construction

Finish:

Formulated for high-durability and long lasting color

Cold Weather Starting:

Minimum starting temperature is -40°C (-40°F)

Maximum Ambient Temperature:

Suitable for use in 40°C (104°F)

Housing:

Precision die cast aluminum housing, lens frame

Mounting:

Surface plate and Junction box

Green Technology:

Mercury and UV-free. RoHS compliant components.

Gaskets:

High Temperature Silicone

Other

Patents:

The LPACK design is protected under patents in the U.S. Pat. D608,040, Canada Pat. 130,243, China Pat. 200930183252.2, and pending patents in Taiwan and Mexico.

Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at

Equivalency:

Equivalent to 70W Metal Halide

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Optical

BUG Rating:

B1 U0 G0

Copyright © 2018 RAB Lighting Inc. All Rights Reserved Note: Specifications are subject to change at any time without notice

WPLED10

RAB Outdoor

Dimensions

Features

- High performance LED light engine
- Maintains 70% of initial lumens at 100,000 hours
- Weatherproof high temperature silicone gaskets
- Superior heat sinking with die cast aluminum housing and external fins
- 5-Year, No-Compromise Warranty

Ordering Matrix

Family	Wattage	Color Temp	Sensor	Surface Plate	Surface Place	Finish	Photocell	Other Options
WPLED								
	10 = 10W **13** = 13W	**Blank** = 5000K (Cool) **Y** = 3000K (Warm) **N** = 4000K (Neutral)	**Blank** = No Sensor **MS** = Mini Sensor	**Blank** = No Surface Plate	**S** = Surface Plate	**Blank** = Bronze **W** = White	**Blank** = No Photocell **/PC** = 120V Button **/PCS** = 120V Swivel **/PC2** = 277V Button	**USA** = BAA Compliant **Blank** = Standard

Copyright © 2018 RAB Lighting Inc. All Rights Reserved Note: Specifications are subject to change at any time without notice