ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



WPLED18 *DISCONTINUED* 18W LED WLPK 50K

RAB LIGHTING

Catalog Number	WPLED18
Manufacturer	RAB LIGHTING
Description	Wall Packs 2859 Lumens Wpled 18W Bronze
Weight per unit	6.8 (lbs/each)
Product Category	Led Wallpacks

Features

Voltage Rating	120/277
Wattage	18
Average Life	100000
Lumens	2624

Descriptions

Description	*DISCONTINUED* 18W LED WLPK 50K
Long Description	Wall Packs 2859 Lumens Wpled 18W Bronze
Product Type	Wallpk 18W Cool W/ Backplate
Special Features	Standard
Extra Long Description	RAB WPLED18 WALLPK 18W COOL W/ BACK

Manufacturer Information

Brand	RAB Lighting Inc
	Rab Lighting
GTIN	00019813191027
Manufacturers Part Number	WPLED18
UPC	885360

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Wallpack

Packaging

Carton	1
Weight Per Each	6.8 (lbs/each)

WPLED18



Ultra-high efficiency LED 18 Watt wall pack. patent-pending thermal management system. 100,000 hour L70 lifespan. 5-year, no-compromise warranty.

Color: Bronze

Weight: 6.9 lbs

Project:	Type:
Prepared By:	Date:

Driver Info

Type	Constant Current
120V	0.15A
208V	0.09A
240V	0.08A
277V	0.07A
Input Watts	21W

LED Info

Watts	18W
Color Temp	5000K (Cool)
Color Accuracy	70 CRI
L70 Lifespan	100,000 Hours
Lumens	2,859 lm
Efficacy	136.1 lm/W

Technical Specifications

Compliance

UL Listed:
Suitable for wet locations. Suitable for mounting within 4ft (1.2m) of the ground.

IESNA LM-79 & LM-80 Testing:
RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

DLC Listed:
This product is listed by Design Lights Consortium (DLC) as an ultra-efficient premium product that qualifies for the highest tier of rebates from DLC Member Utilities. Designed to meet DLC 5.1 requirements.
DLC Product Code: P0000175I

Performance

Lifespan:
100,000-Hour LED lifespan based on IES LM-80 results and TM-21 calculations

Wattage Equivalency:
Equivalent to 100W Metal Halide

LED Characteristics

LED:
Multi-chip, high-output, long-life LED

Color Consistency:
7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

Color Stability:
LED color temperature is warrantied to shift no more than 200K in color temperature over a 5-year period

Color Uniformity:
RAB's range of Correlated Color Temperature follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

Construction

Maximum Ambient Temperature:
Suitable for use in up to 40°C (104°F)

Cold Weather Starting:
The minimum starting temperature is -40°C (-40°F)

Thermal Management:
Superior heat sinking with external Air-Flow fins

Finish:
Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color

Reflector:
Semi-specular, vacuum-metalized polycarbonate

Gaskets:
High-temperature silicone gaskets

Housing:
Die-cast aluminum housing, lens frame and mounting arm

Mounting:
Heavy-duty 1/2" thread mounting arm with "O" ring seal & stainless steel screws

Green Technology:
Mercury and UV free. RoHS-compliant components.

Electrical

Driver:
Constant Current, Class 2, 120-277V, 50/60Hz, 120V: 0.15A, 208V: 0.09A, 240V: 0.08A, 277V 0.07A

Dimming Driver:
Driver includes dimming control wiring for 0-10V dimming systems. Requires separate 0-10V DC dimming circuit. Dims down to 10%.

THD:
14.21% at 120V, 10.51% at 277V

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice

Technical Specifications (continued)

Power Factor:
97.4% at 120V, 95.1% at 277V

Other

Patents:
The design of WPLED18 is protected by US patent D608,040, Canada patent 138280, and China patent CN301649064S

Warranty:
RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Replacement:
Replaces 150W Metal Halide

Buy American Act Compliance:
RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Optical

BUG Rating:
B1 U0 G0

Dimensions



Features

- Ultra-high efficiency LED 18 Watt wall pack
- Replaces 100W Metal Halide Wall packs
- 100,00-Hour LED Lifespan
- 5-Year, No-Compromise Warranty

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice

Ordering Matrix

Family	Wattage	Color Temp	Finish	Emergency Battery Backup	Options	Other Options
WPLED	18					
	18 = 18W	**Blank =** 5000K Cool **N =** 4000K Neutral **Y =** 3000K Warm	**Blank =** Bronze **W =** White	**Blank =** No Battery Backup **/E =** Standard Battery Backup **/EC =** Battery Backup with Cold Start	**Blank =** No Option **/PCS =** 120V Swivel Photocell **/PC =** 120V Button Photocell **/PC2 =** 277V Button Photocell	**Blank =** Standard **USA =** BAA Compliant

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice