

AVIATION SNIPS

Offset & Bulldog



**KLEIN
TOOLS®**

Aviation Snips – Offset & Bulldog

KLEIN TOOLS

For Professionals... Since 1857®

Introducing Klein Tools New Offset and Bulldog Aviation Snips

Offset aviation snips are the tradesman's choice for cutting sheet metal. They easily cut sheet metal on the curve without binding, and they keep the user's hand above and away from the metal. **Bulldog aviation snips** are great for short notch cuts in thick or multiple thicknesses of sheet metal, like rolled seams and S-cleats. No matter which version you choose, Klein's new aviation snips have high quality features for long-lasting performance.

Features

Offset blades keep user's hand above material being cut and flow material away from the blades. (Available only on Cat. Nos. 2100L, 2101R, and 2102S.)

Meets or exceeds ANSI/ASME quality standard B107.16M.

Spring-loaded for self-opening action.

Handle contour and maximum 5.5" (139.7 mm) opening provide easier gripping and strong cutting pressure.

Pictured: 2100L

Forged and heat treated steel blades for strength and durability.

Blade adjustment bolt for easy readjustments.

Closure latch for blade protection.

Heavy gauge steel handles for extra strength.

Textured, comfort grips are color-coded by cutting pattern.

Handy hang hole.

Capacities:

- Offset blades – cut 18 gauge cold-rolled sheet metal and 22 gauge stainless steel sheet metal.
- Bulldog/Notch blades – notch or trim 16 gauge cold-rolled sheet metal and 18 gauge stainless steel sheet metal.

⚠ WARNINGS:

- Always wear approved eye protection.
- Never use on or near live electrical circuits.

Ordering Information

	Cat. No.	UPC No. 0-92644+	Description	Length of Cut	Handle Color	Closed Overall Length	Weight (lbs.)
NEW!	2100L	76023-5	Offset Left Snips	1-1/4" (32 mm)	Red	9-1/2" (241 mm)	0.97
NEW!	2101R	76024-2	Offset Right Snips	1-1/4" (32 mm)	Green	9-1/2" (241 mm)	0.98
NEW!	2102S	76025-9	Offset Straight Snips	1-1/2" (38 mm)	Yellow	9-1/2" (241 mm)	0.97
NEW!	2103	76026-6	Bulldog/Notch Snips	7/8" (22 mm)	Yellow	9-1/4" (235 mm)	0.87
	1100L	76006-8	Regular Left Snips	1-3/8" (35 mm)	Red	9-3/4" (248 mm)	0.90
	1101R	76008-2	Regular Right Snips	1-3/8" (35 mm)	Green	9-3/4" (248 mm)	0.92
	1102S	76010-5	Regular Straight Snips	1-1/2" (38 mm)	Yellow	10-1/8" (257 mm)	0.90
	86553	86553-4	Straight-Hand Seamer	–	Blue	8-3/8" (213 mm)	1.45
	86552	86552-7	Offset-Hand Seamer	–	Blue	8" (203 mm)	1.46
	86551	86551-0	Hand Notcher	–	Blue	8-1/2" (216 mm)	1.00
	86550	86550-3	5-Blade Crimper	–	Blue	9" (229 mm)	1.00
	76011B	76020-4	Nibbler Cutter w/Blade	–	–	–	0.35



KLEIN TOOLS

For Professionals... Since 1857®

Chicago, IL 60659-9033
www.kleintools.com