

NVENT ERICO CADWELD PLUS WELDING MATERIAL, F20, 115PLUSF20

CATALOG NUMBER

115PLUSF20



nVent ERICO Cadweld Plus Welding Material, F20, allows for an expedited, permanent grounding connection using pre-measured, self-contained cups. Each package of welding material can be easily placed into the mold and safely ignited with the nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit to create an irreversible bond.

CERTIFICATIONS



FEATURES

Mixture consists mainly of copper oxide and aluminum

Primarily used in grounding and bonding applications

Integrated welding material package

Color coding by size for easy identification

Electronic ignition

No starting material required

Non-explosive

Not subject to spontaneous ignition

See specific nVent ERICO Cadweld connection details to determine welding material requirements

PRODUCT ATTRIBUTES

Color Code Ring: Orange

Complies With: EN IEC® 62561-1 permanent connection

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER

NVENT ERICO CADWELD PLUS WELDING MATERIAL, F20, 115PLUSF20

CATALOG NUMBER

115PLUSF20



nVent ERICO Cadweld Plus Welding Material, F20, allows for an expedited, permanent grounding connection using pre-measured, self-contained cups. Each package of welding material can be easily placed into the mold and safely ignited with the nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit to create an irreversible bond.

CERTIFICATIONS



FEATURES

Mixture consists mainly of copper oxide and aluminum

Primarily used in grounding and bonding applications

Integrated welding material package

Color coding by size for easy identification

Electronic ignition

No starting material required

Non-explosive

Not subject to spontaneous ignition

See specific nVent ERICO Cadweld connection details to determine welding material requirements

PRODUCT ATTRIBUTES

Color Code Ring: Orange

Complies With: EN IEC® 62561-1 permanent connection

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER