



## Type 3R Wiring Trough – Powder Coated

- Designed to protect wiring indoors from dripping water, or outdoors from rain, sleet and snow
- Stock inventory sizes from 4x4x12 to 12x12x144
- Custom sizes and modifications available

### SPECIFICATIONS

- Formed from code gauge, low carbon steel
- Drip shield top, seam-free sides
- Accumulation-free bottom
- Slip-on cover without gasket
- Embossed mounting holes provided
- **New padlock provision available on most sizes**

### FINISH

- Standard: Gunsmoke Gray Powder Coated
- Optional powder coat colors and custom silkscreen printing available (*see pg. 48*)

### INDUSTRY STANDARDS

- Type 3R - UL 870: Intended for outdoor use primarily to provide a degree of protection against rain, sleet, and damage from external ice formation.
- RoHS compliant

CATALOG NUMBER	UPC (761515)	SIZE (D"xH"xL")	WGT	LIST PRICE
4412GRTNK	14060	4x4x12	4	\$60.00
4424GRTNK	14070	4x4x24	7	\$88.89
4436GRTNK	14077	4x4x36	10	\$115.56
4448GRTNK	14084	4x4x48	14	\$142.22
44120GRTNK	14100	4x4x120	40	\$355.56
6612GRTNK	14181	6x6x12	6	\$84.44
6618GRTNK	14183	6x6x18	8	\$111.11
6624GRTNK	14190	6x6x24	11	\$120.00
6636GRTNK	14197	6x6x36	16	\$160.00
6648GRTNK	14204	6x6x48	21	\$200.00
6660GRTNK	14211	6x6x60	26	\$240.00
6672GRTNK	14218	6x6x72	32	\$288.89
6696GRTNK	14220	6x6x96	45	\$488.89
66120GRTNK	14222	6x6x120	53	\$577.78
8812GRTNK	14295	8x8x12	9	\$115.56
8824GRTNK	14309	8x8x24	15	\$177.78
8836GRTNK	14314	8x8x36	22	\$222.22
8848GRTNK	14321	8x8x48	28	\$311.11
8860GRTNK	14328	8x8x60	35	\$377.78
8872GRTNK	14335	8x8x72	42	\$435.56
8896GRTNK	14340	8x8x96	50	\$622.22
88120GRTNK	14350	8x8x120	60	\$822.22
101024GRTNK	14424	10x10x24	20	\$266.67
101036GRTNK	14426	10x10x36	28	\$355.56
101048GRTNK	14433	10x10x48	37	\$444.44
101060GRTNK	14440	10x10x60	45	\$533.33
101072GRTNK	14447	10x10x72	60	\$622.22
101096GRTNK	14449	10x10x96	85	\$800.00
1010120GRTNK	14450	10x10x120	100	\$1066.67
121224GRTNK	14473	12x12x24	25	\$311.11
121236GRTNK	14475	12x12x36	35	\$488.89
121248GRTNK	14482	12x12x48	45	\$577.78
121260GRTNK	14489	12x12x60	60	\$777.78
121272GRTNK	14496	12x12x72	70	\$844.44
121296GRTNK	14498	12x12x96	85	\$1044.44
1212120GRTNK	14499	12x12x120	110	\$1222.22
1212144GRTNK	14500	12x12x144	153	\$1622.22

