



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



12126SCG Encl 12X12X6 N3 N12 Galv SC Gasketed

Cooper B-Line/Cable Tray

Catalog Number	12126SCG
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Type 3/3R Junction Boxes, 12" Height, 6" Length, 12" Width, Nema 3 and 12, Screw Cover, SCG Enclosure, Surface Mounted, Small Single Door, No Mounting Provisions, Galvanized Steel, Oil-Resistant Gasket, Gasketed Screws
Weight per unit	14.2 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

Features

dimensions	6.0000 IN X 12.0000 IN X 12.0000 IN
Material	Galvanized Steel
Mounting Type	Surface

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	12.00 In Width X 6.00 In Depth X 12.00 In Height
------	--

Descriptions

Description	ENCL 12X12X6 N3 N12 GALV SC GASKETED
extra long description	B-LINE 12126 SCG TYPE 3 GLV GASKETE
Features	Eaton's B-Line series junction boxes provide reliable environmental protection and are used as commercial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series Type 3/3R junction boxes, 12" height, 6" length, 12" width, NEMA 3 and 12, Screw cover, SCG enclosure, Surface mounted, Small single door, No mounting provisions, Galvanized steel, Oil-resistant gasket, gasketed screws
Product Type	Type 3 GLV Gasketed SC 12X12X6

Manufacturer Information

Brand	Eaton
GTIN	00782051108644
Manufacturers Part Number	12126 SCG
UPC	782051108644

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 3/3R junction boxes



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	14.2

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Safety and Security Systems Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Aviation Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Power Distribution and Controls Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other Commer
nema rating	312
standard	CSA C22.2, UL 50, NEMA