



Catalog Number: 121272-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572101524


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 12x12
Straight Section Length: 72
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CAT. NO.	U/L LABEL
121272-GSC3R	1002943
RC-121272-GSC3R	1125051
SPRSCG-121272	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	FRONT
3	6	1001290	SCREW, 10-32 X 5/16
4	1	1002884	LABEL RATING
5	1	(SEE CHART)	UL LABEL, WIREWAY



SUFFIX	FINISH	WELDMENT NO.	FRONT NO.	K.O.s INSTALLED
NONE	MILBANK LIGHT GRAY	1164882	1004432	YES
-NK	MILBANK LIGHT GRAY	1164883	1004432	NO
-NP	NONE	1164884	1006309	YES
-NK-NP	NONE	1164885	1006309	NO

Material:	16 GA. GALV. STEEL	
Shear/ Die#:		
Finish:	SEE CHART	
Part Wt.:		
Tolerances:	Third Angle	
Unless Specified Otherwise		
X.X	±.1	
X.XX	±.03	
X.XXX	±.015	
X*	±2*	
Scale:	NTS	Checked By:
Drawn By:	D.F.	Approved By:

MILBANK
ENERGY AT WORK

General Offices: Kansas City, MO

Title: SCREW COVER WIREWAY
NEMA TYPE 3R

NEMA DWG.: #298

REV.	DATE	DESCRIPTION	BY
D2	5/24/13	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN (ECO #23995)	D.F.

Catalog No.:	(SEE CHART)
Customer:	
Drawing No.:	1004645
Date:	5/24/13
Sheet	1 of 1



Catalog Number: 121272-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572101524


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 12x12
Straight Section Length: 72
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CAT. NO.	U/L LABEL
121272-GSC3R	1002943
RC-121272-GSC3R	1125051
SPRSCG-121272	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	FRONT
3	6	1001290	SCREW, 10-32 X 5/16
4	1	1002884	LABEL RATING
5	1	(SEE CHART)	UL LABEL, WIREWAY



SUFFIX	FINISH	WELDMENT NO.	FRONT NO.	K.O.s INSTALLED
NONE	MILBANK LIGHT GRAY	1164882	1004432	YES
-NK	MILBANK LIGHT GRAY	1164883	1004432	NO
-NP	NONE	1164884	1006309	YES
-NK-NP	NONE	1164885	1006309	NO

Material:	16 GA. GALV. STEEL	
Shear/ Die#:		
Finish:	SEE CHART	
Part Wt.:		
Tolerances:	Third Angle	
Unless Specified Otherwise		
X.X	±.1	
X.XX	±.03	
X.XXX	±.015	
X*	±2*	
Scale:	NTS	Checked By:
Drawn By:	D.F.	Approved By:

MILBANK
ENERGY AT WORK

General Offices: Kansas City, MO

Title: SCREW COVER WIREWAY
NEMA TYPE 3R

NEMA DWG.: #298

REV.	DATE	DESCRIPTION	BY
D2	5/24/13	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN (ECO #23995)	D.F.

Catalog No.: (SEE CHART)

Customer:

Drawing No.: **1004645**

Date: 5/24/13 Sheet 1 of 1