



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1226W SW Maintd Control 20A 120/277V (DPDT) WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 1226W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Double-Pole, Double-Throw Switch, 20A, 120/277V. |
| Weight per unit | 0.3120 (lbs/each) |
| Product Category | Manual Motor Switches & Accy. |

Features

| | |
|-----------------------|-------------------|
| amperage rating | 20 |
| Contact Configuration | NO |
| Contact Rating | 20Amp, 120/277Vac |
| insulation | Bare |
| Poles | dpdt |
| Voltage Rating | 120/277 |
| Wattage | 2 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | SW MAINTD CONTROL 20A 120/277V (DPDT) WH |
| extra long description | P&S 1226W SW MAINTD CNTRL 20A 120/ |
| Long Description | Double-Pole, Double-Throw Switch, 20A, 120/277V. |
| Product Type | SW Maintd CNTRL 20A 120/277V (DPDT) W |
| Special Features | Oversized silver alloy contacts, side wired, can be mounted in standard device box, |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007122640 |
| Manufacturers Part Number | 1226-W |
| UPC | 785007122640 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | REVERSING |
| Type | Manual Controller Switch |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.312 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---------------------------------|
| Application | Industrial |
| Enclosure | Box or NEMA 1 sheet steel |
| Mounting | WALL |
| standard | UL Listed |