



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1222GY Switch, Hubpro, 2-Pole, 20A 120/277V, Gy *Hubbell Wiring Devices*

Catalog Number	1222GY
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Hubbell- Pro Series, Toggle Switches, General Purpose Ac, Double Pole, 20A 120/277V Ac, Back and Side Wired, Gray
Weight per unit	0.0770 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Positive Snap
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
operating cycles	50,000
pallet quantity	4400
Poles	Double Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540

### Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

### Descriptions

Description	SWITCH, HUBPRO, 2-POLE, 20A 120/277V, GY
extra long description	HWDK 1222GY SWITCH, HUBPRO, 2-POLE,
Long Description	Switches and Lighting Controls, Hubbell- PRO Series, Toggle Switches, General Purpose AC, Double Pole, 20A 120/277V AC, Back and Side Wired, Gray
Product Type	Switch, Hubpro, 2-Pole, 20A 120/277V, Gy
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585181394
Manufacturers Part Number	1222GY
series	Heavy Duty
UPC	783585181394



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	TOGGLE

## Packaging

Carton	1
Package	10
Weight Per each	0.077

## Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed