



## Chain



**Working Load Limit Designates The Maximum Stress In Pounds Which Should Ever Be Applied To Chain. This Refers To Chain In The Best Condition, When New, And When The Load Is Applied Uniformly To A Straight, Untwisted Length Of Chain.**

***Warning: Working Load Limits Must Not Be Exceeded.***

| Barcode | Catalog Number | Type        | Finish    | Size | Length    | Package Style | Work Load | Price Per Unit |
|---------|----------------|-------------|-----------|------|-----------|---------------|-----------|----------------|
| 20006   | 14JC           | Jack        | Zinc      | #14  | 100 Foot  | Reel          | 16 lbs    | \$54.00        |
| 20004   | 12JC           | Jack        | Zinc      | #12  | 100 Foot  | Reel          | 29 lbs    | \$64.24        |
| 20005   | 12JCB          | Jack        | Zinc      | #12  | 100 Foot  | Boxed         | 29 lbs    | \$60.80        |
| 19976   | 12JC300        | Jack        | Zinc      | #12  | 300 Foot  | Boxed         | 29 lbs    | \$180.00       |
| 19979   | 12JC300P       | Jack        | Zinc      | #12  | 300 Foot  | Pail          | 29 lbs    | \$200.96       |
| 20003   | 12JC-5C        | Jack        | Zinc      | #12  | 500 Foot  | Reel          | 29 lbs    | \$341.20       |
| 35019   | 12JCM          | Jack        | Zinc      | #12  | 1000 Foot | Pail          | 29 lbs    | \$584.80       |
| 20007   | 12JCSS         | Jack        | Stainless | #12  | 100 Foot  | Boxed         | 29 lbs    | \$396.20       |
| 20002   | 10JC           | Jack        | Zinc      | #10  | 100 Foot  | Reel          | 43 lbs    | \$109.68       |
| 19977   | 10JC300        | Jack        | Zinc      | #10  | 300 Foot  | Boxed         | 43 lbs    | \$273.84       |
| 19990   | 10JC300P       | Jack        | Zinc      | #10  | 300 Foot  | Pail          | 43 lbs    | \$294.80       |
| 20008   | 35SC           | Sash        | Zinc      | #35  | 100 Foot  | Boxed         | 106 lbs   | \$196.00       |
| 23014   | 3DLC           | Double Loop | Zinc      | #3   | 100 Foot  | Boxed         | 90 lbs    | \$81.36        |
| 19978   | 2DLC           | Double Loop | Zinc      | #2   | 100 Foot  | Reel          | 115 lbs   | \$129.36       |
| 23012   | 1/0DLC         | Double Loop | Zinc      | 1/0  | 100 Foot  | Reel          | 200 lbs   | \$127.60       |
| 23010   | 2/0DLC         | Double Loop | Zinc      | 2/0  | 100 Foot  | Boxed         | 255 lbs   | \$140.40       |



## S-Hooks



**S-Hooks Are Made From Low Carbon Steel For Assembling Chain Or Attaching Accessories To Chain.  
S-Hooks Are Not Heat Treated.**


***Do Not Use For Overhead Lifting.***

**For Maximum Strength, All S-Hooks Should Be Closed When Attached To Chain Or Any Other Item.**

| Barcode | Catalog Number | Overall Length | Wire Size | Package Qty | Package Style | Shelf Pack Qty | Case Qty | Price Per Pack |
|---------|----------------|----------------|-----------|-------------|---------------|----------------|----------|----------------|
| 20010   | 1SH            | 1"             | 11 Gauge  | 100         | Box           | 5              | 45       | \$14.12        |
| 96398   | 1SHJ           | 1"             | 11 Gauge  | 100         | Jar           | 6              | 24       | \$15.64        |
| 20012   | 112SH          | 1-1/2"         | 12 Gauge  | 100         | Box           | N/A            | 22       | \$17.16        |
| 96400   | 112SHJ         | 1-1/2"         | 12 Gauge  | 100         | Jar           | 6              | 12       | \$20.44        |
| 20014   | 2SH            | 2"             | 6 Gauge   | 100         | Box           | N/A            | 16       | \$40.40        |
| 20016   | 212SH          | 2-1/2"         | 5/16"     | 50          | Box           | N/A            | 12       | \$63.40        |



## Fluorescent Fixture Hook



Mini Bulk Is Sold & Priced Per Piece. Must Be Purchased In Standard Pack Quantity.

| Barcode | Catalog Number | Type    | Standard Pack | Price Per Piece |
|---------|----------------|---------|---------------|-----------------|
| 91125   | MBEVHOOK       | Top/End | 50            | \$0.5544        |
| 91126   | MBSVHOOK       | Side    | 50            | \$0.5544        |



## Tie Wire



Tie Wire Is Priced & Sold Per Spool  
Tie Wire Must Be Purchased In Standard Pack

| Barcode | Catalog Number | Gauge | Wire Type    | Standard Pack | Price Per Spool |
|---------|----------------|-------|--------------|---------------|-----------------|
| 85000   | TWP5PK         | 16    | Plain Finish | 5             | \$21.00         |
| 85002   | TW             | 16    | Plain Finish | 20            | \$17.72         |
| 85003   | TWG18          | 18    | Galvanized   | 20            | \$23.40         |
| 85001   | TWG5PK         | 16    | Galvanized   | 5             | \$28.48         |
| 85004   | TWG            | 16    | Galvanized   | 20            | \$24.68         |



## Ceiling Wire




| Barcode | Catalog Number | Gauge | Length  | Wire Type  | Tube Quantity | Price Per Tube |
|---------|----------------|-------|---------|------------|---------------|----------------|
| 85009   | CW1212         | 12    | 12 Foot | Galvanized | 100 pieces    | \$284.40       |




## Acoustical Screws



| Barcode | Catalog Number | Size    | Type       | Jar Qty | Shelf Pack Qty | Case Qty | Price Per Jar |
|---------|----------------|---------|------------|---------|----------------|----------|---------------|
| 97410   | 14X2AETJ       | 1/4 x 2 | Self Drill | 100     | 6              | 12       | \$73.94       |
| 97411   | 14X3AELSJ      | 1/4 x 3 | Lag        | 50      | 6              | 12       | \$16.96       |



## Acoustical Screws Installation Tool



| Barcode | Catalog Number | Description       | Standard Pack | Price Per Piece |
|---------|----------------|-------------------|---------------|-----------------|
| 97412   | 1900           | Acoustical Driver | 1             | \$4.40          |

# Notes

# Electrical Products - Fixture Hanging

Notes

**Electrical Products - Fixture Hanging**