ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3205 Axtell
Clovis, NM 88101-0000
Phone: 5757422504
Fax: 5757422508



13017LTWB0X SWITCH TOGGLE SP LT 15A 120V GRD WH

EATON WIRING DEVICES

Catalog Number	13017LTWB0X
Manufacturer	EATON WIRING DEVICES
Description	Eaton toggle switch, Lighted, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Polycarbonate
Weight per unit	0.1150 (lbs/each)
Product Category	Gen Purpose Switches

Features

Material	Polycarbonate
Poles	Single-pole
Voltage Rating	120 V
Amperage Rating	15
Dimensions	1.3100 IN X 0.8800 IN X 3.2800 IN

Descriptions

Description	SWITCH TOGGLE SP LT 15A 120V GRD WH
Features	Eaton's Arrow Hart residential grade switches are engineered for smooth action and years of safe, dependable service - no matter what the application, type of load or use.
Long Description	Eaton toggle switch, Lighted, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Polycarbonate
Product Type	Switch Toggle SP LT 15A 120V GRD WH
Special Features	Lighted, box
Extra Long Description	EWD 1301-7LTWBOX Switch Toggle SP L

Manufacturer Information

Brand	Eaton
	Eaton Wiring Devices
GTIN	00032664519468
Manufacturers Part Number	1301-7LTWBOX
UPC	781430

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	TOGGLE SWITCH

3205 Axtell
Clovis, NM 88101-0000
Phone: 5757422504
Fax: 5757422508

Packaging

Carton	10
Package	100
Weight Per Each	0.1150 (lbs/each)

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Standard	NOM,cULus Listed,RoHS Compliant

Specifications



Photo is representative





Eaton 1301-7LTWBOX

Eaton toggle switch, Lighted, #14-10 AWG, 15A, Flush, 120V, Side and push, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Polycarbonate

General specifications	
PRODUCT NAME	Eaton toggle switch
CATALOG NUMBER	1301-7LTWBOX
UPC	032664519468
PRODUCT LENGTH/DEPTH	1.31 in
PRODUCT HEIGHT	3.28 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.115 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Toggle switch

Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Lighted, box
TYPE	Toggle switch
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
NUMBER OF POLES	Single-pole
APPLICATION	Residential
WIRING METHOD	Side and push
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	MLV LED HAL Motor Control FLR INC CFL Fan ELV
MATERIAL	Polycarbonate
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
COLOR	White

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1301-7LTWBOX Residential grade toggle switches spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.