



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



13106A6513 Comet 8" STD Prox 20-264 Vac/DC With 6' Cable Eaton Corp

Catalog Number	13106A6513
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Diffuse Reflective, Forward Viewing, Output On, 6.6 FT, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, PVC, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

Dimensions and Weight

Height	0.71
Length	2.2
Width	0.47

Descriptions

Description	COMET 8" STD PROX 20-264 VAC/DC WITH 6' CABLE
extra long description	ETN 13106A6513 18MM,8" STD PROX 20-
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor,Diffuse Reflective, Forward Viewing, Output ON, 6.6 ft, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, PVC, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	18MM, 8" STD Prox 20-264 Acdc W/6' CBL

Manufacturer Information

Brand	Eaton
GTIN	00782113823454
Manufacturers Part Number	13106A6513
UPC	782113823454

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.67



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature	-40° to 158°F (-40° to 70°C)
standard	UL Recognized,cUL Recognized