

# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave 76301-0000, TX Wichita Falls Phone: 940-257-6832 Fax: 940-257-6833



# 1418N4S16LL12 36X36X12 N4X SS6 CH Clamp CVR Hammond MFG.

Catalog Number	1418N4S16LL12
Manufacturer	Hammond MFG.
Description	N4X Wallmount Encl W/Panel - 36 X 36 X 12 - 316 SS
Weight per unit	136.0 (lbs/each)
Product Category	Nema Types 4.8, 4X Metallic Enc
atures	

#### **Features**

Material Stainless Steel

#### Material, Color, and Finish

Color Unpainted

### **Dimensions and Weight**

Size 36 in x 36 in x 12 in

#### **Descriptions**

Description

extra long description	HMND 1418N4S16LL12 NEMA 4 316SS ENC
Long Description	N4X Wallmount Encl w/panel - 36 x 36 x 12 - 316 SS
Product Type	Nema 4 316SS Encl 36X36X12
Special Features	Formed 14 gauge 304 or 316 stainless steel. Smooth, continuously welded seams without knockouts, cutouts or holes. Door stiffeners are provided in the larger enclosures for extra rigidity. Welded brackets provide for enclosure mounting. Formed lip on door and enclosure excludes flowing liquids and contaminants. Stainless steel continuous hinge on door may be removed by pulling the stainless steel hinge pin. Door is secured with easily operated stainless steel clamps. Provision for padlocking. Seaml

36X36X12 N4X SS6 CH CLAMP CVR

#### **Manufacturer Information**

Brand	Hammond MFG.
GTIN	00623980149172
Manufacturers Part Number	1418N4S16LL12
UPC	623980149172

### **Taxonomies, Classifications, and Categories**

Category Description	STEEL JUNCTION BOXES
Туре	Type 4X Stainless Steel Wallmount Enclosure

## **Packaging**

Carton	
Weight Per each	136



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave 76301-0000, TX Wichita Falls Phone: 940-257-6832 Fax: 940-257-6833

	iluai us
Application	Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures. Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem
Mounting	WALL
nema rating	13;3R;4X
standard	CSA, UL, CE