



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1412612CHC Encl 14X12X6 N12 Encl *Cooper B-Line/Cable Tray*

Catalog Number	1412612CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 14" Height, 6" Length, 12" Width, Nema 12, Hinged Cover, 12CHC Enclosure, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	13.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	6.0000 IN X 12.0000 IN X 14.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	12.00 In Width X 6.00 In Depth X 14.00 In Height
------	--

Descriptions

Description	ENCL 14X12X6 N12 ENCL
extra long description	B-LINE 14126-12CHC TYPE 12 JIC CONT
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 14" height, 6" length, 12" width, NEMA 12, Hinged cover, 12CHC enclosure, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 Jic Continuous Hinge CVR Enc, 14X12X6
Special Features	Cont. piano hinge, panel mount, plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051750805
Manufacturers Part Number	14126-12CHC
UPC	782051750805

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	12.987

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - OtherInd Facilities & Factories - Facility: Automation and MonitoringCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional Buildings / Structures - Critical PowerInd Facilities & Factories - Facility: Safety and Security SystemsInd Facilities & Factories - Facility: Critical PowerCommercial / Institutional Buildings / Structures - Power Distribution and ControlsInd Facilities & Factories -
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	NEMA,UL 508A,CSA C22.2.