

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301410031](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector, 2 Pole/3 Wire, NEMA 5-15, 125V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130141</a>
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Overview	<a href="#">Heavy-Duty Industrial Wiring Devices</a>
Product Literature Order No	987650-8068
Product Name	Super-Safeway
Receptacle Type	Single
Specialty	N/A
Type	Connector
UPC	78678870302
Woodhead	Yes

**Physical**

Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	No
Net Weight	113.398/g
Poles	2-pole/3-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

**Material Info**

Engineering Number	1547
--------------------	------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/108/2014 (17 Dec  
2014)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

**Search Parts in this Series**

[130141 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301410031](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector, 2 Pole/3 Wire, NEMA 5-15, 125V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                                      LR6837  
UL                                        E10176

**General**

Product Family                      Wiring Devices  
Series                                    [130141](#)  
IP Rating                                N/A  
NEMA Configuration                NEMA 5-15  
Overview                                [Heavy-Duty Industrial Wiring Devices](#)  
Product Literature Order No        987650-8068  
Product Name                         Super-Safeway  
Receptacle Type                      Single  
Specialty                                N/A  
Type                                       Connector  
UPC                                        78678870302  
Woodhead                                Yes

**Physical**

Flange                                    No  
Flip Lid                                  No  
Gender                                    Female  
Length                                    N/A  
Locking Blade                         No  
Net Weight                              113.398/g  
Poles                                       2-pole/3-wire

**Electrical**

Cord Type                                N/A  
Current - Maximum per Contact    15.0A  
GFCI                                       No  
Lighted Connector                    No  
Voltage - Maximum                    125V

**Material Info**

Engineering Number                    1547



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/108/2014 (17 Dec  
2014)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130141](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**