



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



161484QT Encl 16X14X8 N4 CH QTR TRN LTCH

Cooper B-Line/Cable Tray

Catalog Number	161484QT
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 16" Height, 8" Length, 14" Width, Nema 4, Hinged Cover, 4QT Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	17.7 (lbs/each)
Product Category	Nema Type 4 Metallic Enclosure

Features

dimensions	8.0000 IN X 14.0000 IN X 16.0000 IN
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	14.451 IN X 8.445 IN X 17.5 IN
------	--------------------------------

Descriptions

Description	ENCL 16X14X8 N4 CH QTR TRN LTCH
extra long description	B-LINE 16148-4QT TYPE 4 JIC CONT HI
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 16" height, 8" length, 14" width, NEMA 4, Hinged cover, 4QT enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 4 Jic Cont Hinge CVR, 1/4 Turn Latch 16X14X8
Special Features	Continous piano hinge,panel mount,1/4 turn latches

Manufacturer Information

Brand	Eaton
GTIN	00782051881899
Manufacturers Part Number	16148-4QT
UPC	782051881899

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	17.724

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Ind Facilities & Factories - Facility: Power Distribution and Control Ind Facilities & Factories - Mfg. Process Electrification and Control Ind Facilities & Factories - Facility: Automation and Monitoring Ind Facilities & Factories - Industrial Facilities/Factories - Other Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Critical Power Ind Facili
standard	NEMA,UL 50,CSA C22.2.