
ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000



# 18055 Rhino 1/2" White Heat Shrink Tubes

*Newell (Dymo)*

| | |
|---|---|
| Catalog Number | 18055 |
| Manufacturer | Newell (Dymo) |
| Description | Heat Shrink Tube, Polyolefin Material, White, Black Legend Color, 1500 Psi Tensile Strength, 1.5 M Length, 1/2 In (Dia.) Width, 0.5 Mil Thickness |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Markers & Marking Tapes |

## Features

| | |
|---|---|
| Shrink Ratio | 3:1 |
| Voltage Rating | 600 Volt |

## Material, Color, and Finish

| | |
|---|---|
| Color | Black on White |

## Descriptions

| | |
|---|---|
| Additional Information | RoHS Compliant; Tube Width 1/2 Inch; Applicable Standard MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 |
| Commodity Description | Markers & Marking Tapes |
| Description | RHINO 1/2" WHITE HEAT SHRINK TUBES |
| extra long description | HEAT SHRINK TYPE; POLYOLEFIN MATERIAL; BLACK ON WHITE COLOR; 5 FOOT; RHINO 4200 PRINTER TYPE; RHINO[TM] BRAND; ROHS/REACH COMPLIANT; WIDTH 1/2 INCH; VOLTAGE RATING 600 VOLT; SHRINK RATIO 3:1; THICKNESS 0.5 MILLIMETER; TEMPERATURE RATING 257 DEG F; APPLICATION INDUSTRIAL; APPLICABLE STANDARD UL 224, MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 |

## Manufacturer Information

| | |
|---|---|
| GTIN | 00071701180551 |
| Manufacturers Part Number | 784-18055 |
| UPC | 071701180551 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Printers and Labeling |
| Type | HEAT |

## Packaging

| | |
|---|---|
| Carton | 5 |
| Weight Per each | 0.08 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Approval | UL 224 |
| Temperature Rating | 257 Deg F |