



MILBANK
ENERGY AT WORK



18184-SC1-NK

| | |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 18184-SC1-NK |
| Marketing Product Description | 18x4X18 Screw Cover Type 1 UL Listed Steel No Knockouts ANSI 61 Gray Cover With Teardrop Slots Mounting Holes In Back |
| UPC | 784572103016 |
| Length (IN) | 4 |
| Width (IN) | 18 |
| Height (IN) | 18 |
| Weight (LB) | 17 |
| Brand Name | Milbank |
| Type | Screw Cover |
| Application | Enclosure for Mounting Electrical Equipment |
| Standard | UL Listed |
| Number Of Outlet | 0 |
| Material | Steel with Powder Coat Finish |
| Size | 4L x 18W x 18H |
| Color | ANSI 61 Gray |
| Construction | Welded |
| Cable Entry | No Knockouts |
| Mounting | Wall Mount |
| NEMA Rating | Type 1 |
| Hinge Type | No Hinge |

| | |
|---------|-------------------------------------|
| Top | Plain Top |
| Door | Cover |
| Latch | Cover Secured with Plated Screws |
| Support | Formed and Spot Welded |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK
ENERGY AT WORK



18184-SC1-NK

| | |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 18184-SC1-NK |
| Marketing Product Description | 18x4X18 Screw Cover Type 1 UL Listed Steel No Knockouts ANSI 61 Gray Cover With Teardrop Slots Mounting Holes In Back |
| UPC | 784572103016 |
| Length (IN) | 4 |
| Width (IN) | 18 |
| Height (IN) | 18 |
| Weight (LB) | 17 |
| Brand Name | Milbank |
| Type | Screw Cover |
| Application | Enclosure for Mounting Electrical Equipment |
| Standard | UL Listed |
| Number Of Outlet | 0 |
| Material | Steel with Powder Coat Finish |
| Size | 4L x 18W x 18H |
| Color | ANSI 61 Gray |
| Construction | Welded |
| Cable Entry | No Knockouts |
| Mounting | Wall Mount |
| NEMA Rating | Type 1 |
| Hinge Type | No Hinge |

| | |
|---------|-------------------------------------|
| Top | Plain Top |
| Door | Cover |
| Latch | Cover Secured with Plated Screws |
| Support | Formed and Spot Welded |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.