



Catalog Number: 18184-SC1-NK
Item Description: N1 SCREW COVER ENCL NK
UPC Code: 784572103016



Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|------------------|---------|
| 18184-SC1-() | 1002135 |
| RC-18184-SC1-() | 1125021 |
| SPSC-18184 | 1132714 |


| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|--------------------------|
| 1 | 1 | (SEE CHART) | BACK WELDMENT |
| 2 | 1 | (SEE CHART) | COVER PLATE |
| 3 | 1 | (SEE CHART) | U/L LISTING LABEL |
| 4 | 1 | 1002475 | BAG ASSY (GROUND SCREW) |
| 5 | 4 | 1001290 | SCREW, 10-32 X 5/16 |
| 6 | 0.33 | 1002931 | CARTON 3-PER (NOT SHOWN) |



NOTES:



1. PLACE BAG ASSY INSIDE ENCLOSURE (NOT SHOWN).

(APPLY INSIDE BACK)



| SUFFIX | FINISH | WELDMENT NO. | COVER NO. | INSTALL KOs |
|--------|--------------------|--------------|-----------|-------------|
| NONE | MILBANK LIGHT GRAY | 1160238 | 1154419 | YES |
| -NP | NONE | 1160239 | 1003271 | |
| -NK | MILBANK LIGHT GRAY | 1011175 | 1154419 | NO |
| -NK-NP | NONE | 1160240 | 1003271 | |

NEMA DWG.: #117

| | | | |
|--|--------------|---|--|
| Material: | 16 GA. STEEL |  General Offices: Kansas City, MO | |
| Finish: | (SEE CHART) | | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2° | | Title: | 18184 SCREW COVER TYPE 1 ENCLOSURE |
|  | | Catalog No.: | (SEE CHART) |
| Scale: NTS | | Customer: | MILBANK STANDARD |
| Checked By: | | Drawing No.: | 1001553 |
| Drawn By: DY | Approved By: | Date: | 04/26/01 Sheet 1 of 1 |

| | | | | | | |
|---|--------|--|----|--|--|--|
| D | 8/1/12 | DELETE 1002646; ADD 1001290 (ECO #22728) | DF | | | |
|---|--------|--|----|--|--|--|



Catalog Number: 18184-SC1-NK
Item Description: N1 SCREW COVER ENCL NK
UPC Code: 784572103016



Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|------------------|---------|
| 18184-SC1-() | 1002135 |
| RC-18184-SC1-() | 1125021 |
| SPSC-18184 | 1132714 |

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|--------------------------|
| 1 | 1 | (SEE CHART) | BACK WELDMENT |
| 2 | 1 | (SEE CHART) | COVER PLATE |
| 3 | 1 | (SEE CHART) | U/L LISTING LABEL |
| 4 | 1 | 1002475 | BAG ASSY (GROUND SCREW) |
| 5 | 4 | 1001290 | SCREW, 10-32 X 5/16 |
| 6 | 0.33 | 1002931 | CARTON 3-PER (NOT SHOWN) |





NOTES:
 1. PLACE BAG ASSY INSIDE ENCLOSURE (NOT SHOWN).



| SUFFIX | FINISH | WELDMNT NO. | COVER NO. | INSTALL KOs |
|--------|--------------------|-------------|-----------|-------------|
| NONE | MILBANK LIGHT GRAY | 1160238 | 1154419 | YES |
| -NP | NONE | 1160239 | 1003271 | |
| -NK | MILBANK LIGHT GRAY | 1011175 | 1154419 | NO |
| -NK-NP | NONE | 1160240 | 1003271 | |

NEMA DWG.: #117

| | | | |
|---|--------------|---|--|
| Material: | 16 GA. STEEL |  General Offices: Kansas City, MO | |
| Finish: | (SEE CHART) | | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2° | | Title: | 18184 SCREW COVER TYPE 1 ENCLOSURE |
|  Third Angle Projection | | Catalog No.: | (SEE CHART) |
| Scale: NTS | | Customer: | MILBANK STANDARD |
| Checked By: | | Drawing No.: | 1001553 |
| Drawn By: DY | Approved By: | Date: | 04/26/01 Sheet 1 of 1 |

| | | | | | | |
|---|--------|--|----|--|--|--|
| D | 8/1/12 | DELETE 1002646; ADD 1001290 (ECO #22728) | DF | | | |
|---|--------|--|----|--|--|--|