



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1BSS 3/4 Regd/Emt SS Pipe HNGR

*Crouse-Hinds*

Catalog Number	1BSS
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Rigid/Imc Conduit Hanger, Emt and Rigid/Imc, 3/4" Emt Conduit Size, 301 Stainless Steel, 3/4" Rigid Conduit Size, With Bolt
Weight per unit	0.0820 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

dimensions	1.0000 IN X 1.0000 IN X 2.1900 IN
Material	301 Stainless Steel

### Dimensions and Weight

Size	3/4 In (Rigid/EMT)
------	--------------------

### Descriptions

Description	3/4 REGD/EMT SS PIPE HNGR
extra long description	CRS-H 1BSS 3/4 RGD 3/4 EMT STAINLES
Features	Crouse-Hinds series clamps, straps, clampbacks and hangers are used to secure rigid/IMC conduit to mounting surfaces or to provide space between conduit and its mounting surfaces. Available in a variety of materials to meet customer preferences, including steel, malleable iron, stainless steel and hot dip galvanized iron.
Long Description	Eaton Crouse-Hinds series rigid/IMC conduit hanger, EMT and rigid/IMC, 3/4" EMT conduit size, 301 stainless steel, 3/4" rigid conduit size, With bolt
Product Type	3/4 RGD 3/4 Emt Stainless Steel Hanger
Special Features	With Bolt, Weight 7 Lb per 100

### Manufacturer Information

Brand	Eaton
GTIN	00662277011877
Manufacturers Part Number	1BSS
UPC	662277011877

### Taxonomies, Classifications, and Categories

Category Description	CONDUIT HANGERS/STAND OFF STRAPS
Type	CONDUIT HANGER

### Packaging

Carton	100
Weight Per each	0.082



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

standard

UL, cUL