# BUCHANAN ICE CA **Crimp Connectors**

**CAUTION:** Turn off power before preparing wire or installing or removing connectors.

TO INSTALL: Strip wires approximately 3/4" long. Insert wires thru cap and twist. Insert Buchanan C24 or P24 pres-SURE-tool with latch at "A" or alternate tools listed. Crimp and cut flush.

**INSULATE:** with Buchanan 2007 Nylon Insulator

**TO REMOVE:** Snip cap at both ends of one crimp or squeeze alternately 90° apart between crimps.

UL and CSA listed as "pressure type wire connectors" and "fixture-type splicing connectors" for 2-10 #18, 2-7 #16, 2-5 #14, 2-4 #12, 2 #10 stranded and/or solid wire. UL listed for grounding equipment. Consult factory for complete listing.

## **Alternate UL Listed Tools:**

- IDEAL 30-425 Nest back & front Jaw
- T&B WT111M Nest C, AB & B
- T&B WT161 Center Nest
- T&B WT100M or WT1000 Nest for bare Term. A. B. C
- T&B WT112M
- 3M TH220 Nest 22-6 & 22-8
- Panduit CT200 Nest 12-10, 22-14 & 22-10





**COPPER WIRE ONLY** 

### **IDEAL INDUSTRIES, INC.**

Sycamore, IL 60178, U.S.A. 800-435-0705 • www.idealindustries.com ND 7390-2

Made in U.S.A. of US and global components.

CAT. NO. QTY. 2006SB/1,000



## BUCHANAN ICE CA

## **Crimp Connectors**



**CAUTION:** Turn off power before preparing wire or installing or removing connectors.

**TO INSTALL:** Strip wires approximately 3/4" long. Insert wires thru cap and twist. Insert Buchanan C24 or P24 pres-SURE-tool with latch at "A" or alternate tools listed. Crimp and cut flush.

**INSULATE:** with Buchanan 2007 Nylon Insulator

**TO REMOVE:** Snip cap at both ends of one crimp or squeeze alternately 90° apart between crimps.

UL and CSA listed as "pressure type wire connectors" and "fixture-type splicing connectors" for 2-10 #18, 2-7 #16, 2-5 #14, 2-4 #12, 2 #10 stranded and/or solid wire. UL listed for grounding equipment. Consult factory for complete listing.

## **Alternate UL Listed Tools:**

- IDEAL 30-425 Nest back & front Jaw
- T&B WT111M Nest C, AB & B
- T&B WT161 Center Nest
- T&B WT100M or WT1000 Nest for bare Term. A. B. C
- T&B WT112M
- 3M TH220 Nest 22-6 & 22-8
- Panduit CT200 Nest 12-10, 22-14 & 22-10





## **COPPER WIRE ONLY**

### **IDEAL INDUSTRIES, INC.**

Sycamore, IL 60178, U.S.A. 800-435-0705 • www.idealindustries.com

ND 7390-2

Made in U.S.A. of US and global components.

CAT. NO. QTY. 2006SB/1,000

