

Products

- › [Index](#)
- › [Featured Products](#)
- › [Cross Reference](#)
- › [UPC Search](#)

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

2024 -- EMT Set Screw Coupling 1" Trade Size Steel



Product Specifications

Family	EMT Fittings
Fittings Classification	Steel - Set Screw Couplings
Trade Size	1"
Standard Packaging	Carton
Ship Carton Length	11.375
Ship Carton Width	9.00
Ship Carton Height	11.25
WT. PER HU.	24.0
Pallet Qty	4,800
Minimum Pack Qty.	100
Unit Carton Quantity	25
Ship Carton Quantity	100
UPC Number	050169020241
Product UPC-A Labeled	No
Catalog PDF Page	PDF Catalog Page

Applications

- For use in dry locations to couple two ends of EMT conduit
- RACO® steel set screw couplings provide concrete-tight connections when taped
- RACO® set screw couplings are suitable for applications above 600V

Product Features

- All steel construction insures mechanical protection for the raceway
- Tri-head screws (1/2" to 2" trade sizes) may be installed using

- a slotted, Philips, or Robertson head screwdriver
- 2-1/2" to 4" trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
 - All components are zinc electroplated for corrosion protection

Compliances

C / UL / US

Products

- › [Index](#)
- › [Featured Products](#)
- › [Cross Reference](#)
- › [UPC Search](#)

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

2024 -- EMT Set Screw Coupling 1" Trade Size Steel



Product Specifications

Family	EMT Fittings
Fittings Classification	Steel - Set Screw Couplings
Trade Size	1"
Standard Packaging	Carton
Ship Carton Length	11.375
Ship Carton Width	9.00
Ship Carton Height	11.25
WT. PER HU.	24.0
Pallet Qty	4,800
Minimum Pack Qty.	100
Unit Carton Quantity	25
Ship Carton Quantity	100
UPC Number	050169020241
Product UPC-A Labeled	No
Catalog PDF Page	PDF Catalog Page

Applications

- For use in dry locations to couple two ends of EMT conduit
- RACO® steel set screw couplings provide concrete-tight connections when taped
- RACO® set screw couplings are suitable for applications above 600V

Product Features

- All steel construction insures mechanical protection for the raceway
- Tri-head screws (1/2" to 2" trade sizes) may be installed using

- a slotted, Philips, or Robertson head screwdriver
- 2-1/2" to 4" trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility
 - All components are zinc electroplated for corrosion protection

Compliances

C / UL / US