



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2087W Radiant Dead FRNT Self Test Gfci 20A WH

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | 2087W  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Self-Test Gfci Receptacle Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Impact Resistant, 0.2800 LB |
| Weight per unit  | 0.2750 (lbs/each)  |
| Product Category | Gen Purpose Recept & Surge Pro   |

### Features

|                  |                             |
|------------------|-----------------------------|
| actuator         | Control Circuit             |
| amperage rating  | 20                          |
| connection       | Back and side wire          |
| indoor/outdoor   | Indoor                      |
| interrupt rating | 4 to 6 mA                   |
| Mounting Type    | Box                         |
| Number of Gangs  | 1.0                         |
| Outlet Type      | Dead Front, GFCI, Self-Test |
| Poles            | 2                           |
| trip range       | 4 to 6 mA                   |
| Trip Type        | .025 Second Nominal         |
| Voltage Rating   | 125                         |

### Dimensions and Weight

|        |      |
|--------|------|
| Length | 1.03 |
| Width  | 1.73 |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | RADIANT DEAD FRNT SELF TEST GFCI 20A WH |
| extra long description | P&S 2087W RADIANT DEAD FRNT SELF TE     |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN  | 00785007035803 |
| UPC   | 785007035803   |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type                 | Outlet               |

### Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 10    |
| Weight Per each | 0.275 |

## Uses, Certifications, and Standards

|                          |                                   |
|--------------------------|-----------------------------------|
| environmental conditions | 95% Humidity, UL 94 V2            |
| Operating Temperature    | -35°C to +66°C                    |
| standard                 | CULUS, UL, cULus, UL Listed, FSUL |