



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20AC1RED 20A 120/277VAC B+S Wire SP SW RD

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 20AC1RED |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V |
| Weight per unit | 0.1900 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|---------------------|
| action | Single pole |
| amperage rating | 20 |
| Contact Rating | 20 Amp, 120/277 VAC |
| insulation | False |
| Poles | 1 |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | 20A 120/277VAC B+S WIRE SP SW RD |
| extra long description | P&S PS20AC1RED 20A 120/277VAC B+S W |
| Long Description | 1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V |
| Product Type | 20A 120/277VAC B+S Wire SP SW Red |
| Special Features | Back & side wire, locking support, heavy duty toggle |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007196658 |
| Manufacturers Part Number | PS20AC1RED |
| UPC | 785007196658 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | TOGGLE SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.19 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------------------|
| Application | Industrial Spec Grade |
| Enclosure | Nylon |
| Mounting | WALL |
| standard | FEDSPEC, CULUS, UL 498/20, FEDSPEC |