

# Standard size wallplates




## Standard size blank wallplates

### Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang




1-Gang




2-Gang




3-Gang



4-Gang



93630



93631

### Blank - box mounted

Gang	Material	Color suffix	Catalog no.		
1-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5129__	•	•
	Thermoset	A, B, LA, V, W	□ 2129__	•	•
	302/304 Stainless steel	—	□ 93151	•	•
	Brass	—	□ 94151	•	•
2-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5137__	•	•
	Thermoset	A, B, LA, V, W	□ 2137__	•	•
	302/304 Stainless steel	—	□ 93152	•	•
3-Gang	302/304 Stainless steel	—	□ 93153	•	•
4-Gang	302/304 Stainless steel	—	□ 93154	•	•

## Standard size louver

### Product description

Horizontal & vertical

### Louver

Description	Material	Catalog no.		
Horizontal	302/304 Stainless steel	□ 93630	•	•
Vertical	302/304 Stainless steel	□ 93631	•	•

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32

# Standard size wallplates




## Standard size blank wallplates

### Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang




1-Gang




2-Gang




3-Gang



4-Gang



93630



93631

### Blank - box mounted

Gang	Material	Color suffix	Catalog no.	
1-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5129__	• •
	Thermoset	A, B, LA, V, W	□ 2129__	• •
	302/304 Stainless steel	—	□ 93151	• •
	Brass	—	□ 94151	• •
2-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5137__	• •
	Thermoset	A, B, LA, V, W	□ 2137__	• •
	302/304 Stainless steel	—	□ 93152	• •
3-Gang	302/304 Stainless steel	—	□ 93153	• •
4-Gang	302/304 Stainless steel	—	□ 93154	• •

## Standard size louver

### Product description

Horizontal & vertical

### Louver

Description	Material	Catalog no.	
Horizontal	302/304 Stainless steel	□ 93630	• •
Vertical	302/304 Stainless steel	□ 93631	• •

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32