



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



242022 M12 Hackzall Recip Saw Kit

Milwaukee Electric Tool

Catalog Number	242022
Manufacturer	Milwaukee Electric Tool
Description	00045242158584 0045242 045242158584 04524215858 15858 242022 242022 2420-22 M12 Hackzall Hand Saw Kit W/2 Bat Milwaukee Electric Tool 2420 22 Milwaukee Electric Tool 242022 Milwaukee Electric Tool 2420-22 Milwaukee 2420 22 Milwaukee 242022 Milwaukee 2420-22 Milwaukee Electric Tool 2420 22 Milwaukee Electric Tool 242022 Milwaukee Electric Tool 2420-22 Milwaukee Tool 2420 22 Milwaukee Tool 242022 Milwaukee Tool 2420-22 Milwaukee Electric Tool 2420 22 Milwaukee Electric Tool 242022 Milwaukee Electric Tool
Weight per unit	7.6 (lbs/each)
Product Category	Battery Driven Tools

Features

battery	Lithium-Ion
Stroke Length	1/2
Voltage Rating	12

Dimensions and Weight

Length	11
--------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	M12 HACKZALL RECIP SAW KIT
Long Description	00045242158584 0045242 045242158584 04524215858 15858 2420 22 242022 2420-22 M12 HACKZALL HAND SAW KIT W/2 BAT Milwaukee Electric Tool 2420 22 Milwaukee Electric Tool 242022 Milwaukee Electric Tool 2420-22 MILWAUKEE 2420 22 MILWAUKEE 242022 MILWAUKEE 2420-22 MILWAUKEE ELECTRIC TOOL 2420 22 MILWAUKEE ELECTRIC TOOL 242022 MILWAUKEE ELECTRIC TOOL 2420-22 Milwaukee Tool 2420 22 Milwaukee Tool 242022 Milwaukee Tool 2420-22 Milwaukee Electric Tool 2420 22 Milwaukee Electric Tool 242022 Milwaukee Electric Tool
Product Type	M12 Hackzall Hand Saw Kit W/2 Bat
Special Features	Only 11 IN And 2.6 LB For Cutting In Tight Spaces; 12V Lithium-Ion Battery Offers Longer Run-Time And Lighter Weight; Keyless QUIK-LOK Blade Clamp Allows For Quick And Easy Blade Changes; All-Metal Gear Case For Added Durability; Variable Speed Trigger For Increased User Control; Battery Fuel Gauge Displays Remaining Run-Time; Accepts Both HACKZALL And SAWZALL Style Blades (See Related Products For Listing Of HACKZALL Blades); Built-In LED Light Illuminates Work Surface; SfpM: 0 - 3000 SPM; Tool Weight: 2.

Manufacturer Information

Brand	Milwaukee Electric Tool
GTIN	00045242158584
Manufacturers Part Number	2420-22
sub brand	Hackzall M12
UPC	045242158584

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	CORDLESS

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Weight Per each	7.6

Uses, Certifications, and Standards

Application	For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, And PVC
-------------	--