



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2424612 Encl 24X24X6 N12 1DR WM CH *Cooper B-Line/Cable Tray*

Catalog Number	2424612
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 6" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	41.5 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

dimensions	6.0000 IN X 24.0000 IN X 24.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

### Dimensions and Weight

Size	24.00 In Width X 6.00 In Depth X 24.00 In Height
------	--

### Descriptions

Description	ENCL 24X24X6 N12 1DR WM CH
extra long description	B-LINE 24246-12 TYPE 12 SGL-DOOR EN
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 24" height, 6" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 24X24X6
Special Features	Plated door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051800500
Manufacturers Part Number	24246-12
UPC	782051800500

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	41.457

## Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper Converged Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Safety and Security Systems Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Other IT and Datacom - IT and Datacomm - Other Commercial / In
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	NEMA, CSA C22.2., UL 508A