




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 258RTI2 3-1/2" Raintight Dicast Compression Connector

*Bridgeport Fittings*

|                  |  |
|------------------|--|
| Catalog Number   | 258RTI2  |
| Manufacturer     | Bridgeport Fittings                              |
| Description      | 3-1/2" Raintight Insulated Connector, NPT Thread |
| Weight per unit  | 238.0 (lbs/each)                                 |
| Product Category | Die Cast Insulated Straight CO                   |

### Features

|                |                  |
|----------------|------------------|
| Connector Type | Compression      |
| insulation     | Insulated Throat |
| media          | Yes              |

### Dimensions and Weight

|      |       |
|------|-------|
| Size | 3-1/2 |
|------|-------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 3-1/2" RAIN TIGHT DICAST COMPRESSION CONNECTOR           |
| extra long description | BPT 258-RTI2 3-1/2" RAIN TIGHT INS C                     |
| Long Description       | 3-1/2" Raintight Insulated Connector, NPT THREAD         |
| Product Type           | 3-1/2" Raintight Ins Connector                           |
| Special Features       | The Dual Internal sealing rings create a raintight seal. |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Bridgeport     |
| GTIN                      | 00781747192585 |
| Manufacturers Part Number | 258-RTI2       |
| UPC                       | 781747192585   |

### Taxonomies, Classifications, and Categories

|      |                       |
|------|-----------------------|
| Type | Raintight Compression |
|------|-----------------------|

### Trade Size

|            |       |
|------------|-------|
| Trade Size | 3-1/2 |
|------------|-------|

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 6   |
| Weight Per each | 238 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. With Bridgeport's newly redesigned Raintight Compression Connectors, 256-RTI2 thru 259-RTI2, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. These 3-1/2" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAIN TIGHT" clearly cast into the body.

standard

cULus