



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



271921 M18 Fuel Hackzall Kit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 271921 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee 2719 M18 Fuel™ Hackzall® Is The Fastest Cutting and Most Powerful One-Handed Reciprocating Saw. Utilizing A Powerstate Brushless Motor and A Best In Class 7/8 In. Stroke Length, The M18 Fuel™ Hackzall® Cuts Up to 50% Faster Than Competitors. The Compact, One-Handed Design Provides Superior Control and The Ability to Make Cuts In Tight Spaces. The Dual Gear Counter Balance Mechanism Provides Up to 4X Lower Vibration Than Traditional Reciprocating Saws, Resulting In Faster Cut-Starts In Metal A |
| Weight per unit | 10.0 (lbs/each) |
| Product Category | Battery Driven Tools |

Features

| | |
|-----------------|-------|
| Battery Voltage | 18 |
| media | Yes |
| Stroke Length | 0.875 |

Material, Color, and Finish

| | |
|------------------|--------------------|
| Housing Material | Glass Filled Nylon |
|------------------|--------------------|

Dimensions and Weight

| | |
|--------|------|
| Height | 7 |
| Length | 16.3 |
| Width | 5.57 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | M18 FUEL HACKZALL KIT |
| extra long description | MILW 2719-21 Reciprocating Saw Kit |
| Features | Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing! |
| Long Description | The Milwaukee 2719 M18 FUEL™ HACKZALL® is the fastest cutting and most powerful one-handed reciprocating saw. Utilizing a POWERSTATE brushless motor and a best in class 7/8 in. stroke length, the M18 FUEL™ HACKZALL® cuts up to 50% faster than competitors. The compact, one-handed design provides superior control and the ability to make cuts in tight spaces. The dual gear counter balance mechanism provides up to 4x lower vibration than traditional reciprocating saws, resulting in faster cut-starts in metal a |
| Product Type | Reciprocating Saw Kit |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242502974 |
| Manufacturers Part Number | 2719-21 |
| UPC | 045242502974 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
|----------------------|-------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 3 |
| Weight Per each | 10.035 |