



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



272221HD M18 Fuel Super Sawzall Reciprocating Saw Kit

Milwaukee Electric Tool

| | |
|------------------|--|
| Catalog Number | 272221HD |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee M18 Fuel™ Super Sawzall® Generates The Power Of A 15 A Corded Reciprocating Saw, Faster Cuts Than The Legendary Milwaukee 15 A Ac Super Sawzall™; and Up to 150 Cuts In 2 X 12 SPF Per Charge. Designed to Perform In The Toughest Applications The M18™ Fuel Super Sawzall® Combines Milwaukee'S Legendary Performance and Durability With The Portability Of The M18 Platform. The Powerstate™ Brushless Motor Provides 3, 000 SPM and Higher Speeds Under Load For Corded Cutting Performance. Redlink Plus™ In |
| Weight per unit | 17.7 (lbs/each) |
| Product Category | Battery Driven Tools |

Features

| | |
|-----------------|--------------------------|
| Battery Voltage | 18 |
| blade type | Reciprocating Saw Blades |
| charge time | 2.0 |
| media | Yes |
| Switch Type | Trigger |

Material, Color, and Finish

| | |
|------------------|--------------------|
| Blade Material | Steel |
| Housing Material | Glass Filled Nylon |

Dimensions and Weight

| | |
|--------|-----|
| Height | 9.5 |
|--------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | M18 FUEL SUPER SAWZALL RECIPROCATING SAW KIT |
| extra long description | MILW 2722-21HD SUPER SAWZALL® Kit |
| Features | Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing! |
| Long Description | The Milwaukee M18 FUEL™ SUPER SAWZALL® generates the power of a 15 A corded reciprocating saw, faster cuts than the legendary Milwaukee 15 A AC super SAWZALL™; and up to 150 cuts in 2 x 12 SPF per charge. Designed to perform in the toughest applications the M18™ fuel SUPER SAWZALL® combines Milwaukee's legendary performance and durability with the portability of the M18 platform. The POWERSTATE™ brushless motor provides 3,000 SPM and higher speeds under load for corded cutting performance. REDLINK Plus™ in |
| Product Type | Super Sawzall® Kit |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242006489 |
| Manufacturers Part Number | 2722-21HD |
| UPC | 045242006489 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
|----------------------|-------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 17.673 |