



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 27W48 Turnlok Conn IP67 20A 250V L620R

*Pass & Seymour/Legrand*

|                  |                                       |
|------------------|---------------------------------------|
| Catalog Number   | 27W48                                 |
| Manufacturer     | Pass & Seymour/Legrand                |
| Description      | 20A 125V L620R IP67 Turnlok Connector |
| Weight per unit  | 0.8300 (lbs/each)                     |
| Product Category | Plugs, Connectors, Inlets, Out        |

### Features

|                 |   |
|-----------------|---|
| amperage rating | 20  |
| Cord Type       | 12/3 SJ, 14/3 S to 10/3 S, .475" min to .720" max |
| Material        | Rubber  |
| Number of Wires | 3   |
| Phase           | 1   |
| Poles           | 2   |
| Voltage Rating  | 125   |
| Wire Size       | 14 - 10   |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | TURNLOK CONN IP67 20A 250V L620R   |
| extra long description | P&S 27W48 TURNLOK CONN IP67 20A 250  |
| Long Description       | 20A 125V L620R IP67 Turnlok Connector  |
| Product Type           | Turnlok Conn IP67 20A 250V L620R   |
| Special Features       | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |

### Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007033779         |
| Manufacturers Part Number | 27W48                  |
| UPC                       | 785007033779           |

### Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type                 | Locking Connector       |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.83 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

### Application

High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

### environmental conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

### nema rating

L6-20R

### standard

UL Listed, CSA Listed