

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470105](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                  Wiring Devices  
 Series                              [130147](#)  
 IP Rating                          IP67  
 NEMA Configuration            NEMA L15-30  
 Overview                          [Watertite® Wet-Location Wiring Solutions](#)  
 Product Literature Order No    987650-8067  
 Product Name                    Watertite  
 Receptacle Type                Single  
 Specialty                          N/A  
 Type                                Connector  
 UPC                                 78678871333  
 Woodhead                        Yes

**Physical**

Cord Grip Body Size              F4 1"  
 Flange                              No  
 Flip Lid                            No  
 Gender                            Female  
 Length                            N/A  
 Locking Blade                    Yes  
 Poles                                3-pole/4-wire

**Electrical**

Cord Type                         N/A  
 Current - Maximum per Contact 30.0A  
 GFCI                                No  
 Lighted Connector                No  
 Voltage - Maximum               3Ø 250V

**Material Info**

Engineering Number              29W75



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470105](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130147](#)  
 IP Rating      IP67  
 NEMA Configuration      NEMA L15-30  
 Overview      [Watertite® Wet-Location Wiring Solutions](#)  
 Product Literature Order No      987650-8067  
 Product Name      Watertite  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678871333  
 Woodhead      Yes

**Physical**

Cord Grip Body Size      F4 1"  
 Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      Yes  
 Poles      3-pole/4-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      30.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      3Ø 250V

**Material Info**

Engineering Number      29W75



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**