



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2EP3GX2U6T8S33IU 2 Lamp, 2'X2' Static Parabolic, 9 Cell, T8 *Cooper Lighting Solutions*

| | |
|------------------|--|
| Catalog Number | 2EP3GX2U6T8S33IU |
| Manufacturer | Cooper Lighting Solutions |
| Description | 2 U-Lamp, 2'X2' Static Parabolic, 9 Cell, Semi Specular/Low Iridescent Haze 3" Louver, Cee Listed Electronic Ballast, T8 |
| Weight per unit | 14.3 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|-------------------|
| amperage rating | 0.116 at (277V) |
| Ballast Type | Instant Start |
| Lamp Type | T8 (Not Included) |
| Material | Steel |
| Number of Lamps | 2 |
| Voltage Rating | 120-277V |

Material, Color, and Finish

| | |
|-------|---------|
| Style | (blank) |
|-------|---------|

Descriptions

| | |
|------------------------|--|
| Description | 2 LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, T8 |
| extra long description | CLS 2EP3GX-2U6T8S33I-UNV-EB81-U EP3 |
| Long Description | 2 U-Lamp, 2'x2' Static Parabolic, 9 Cell, Semi Specular/Low Iridescent Haze 3" Louver, CEE Listed Electronic Ballast, T8 |
| Product Type | EP3 2 U-Lamp, 2X2 Par, 9 Cell, Semi, T8 |
| Special Features | Provided with CEE-listed energy-saving ballasts |

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | Eaton Lighting |
| GTIN | 00080083520145 |
| Manufacturers Part Number | 2EP3GX-2U6T8S33I-UNV-EB81-U |
| UPC | 080083520145 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | Fluorescent Fixtures & Accessories |
| Type | Paralux III High Performance |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 14.3 |

Uses, Certifications, and Standards

| | |
|-------------|-------------------------------|
| Application | lighting |
| Mounting | Troffer |
| standard | UL/cUL Listed - Damp Location |