



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30087J In-Sure Push-In Wire Conn, 87 5-PRT Gray, 150/Jar

*Ideal*

Catalog Number	30087J
Manufacturer	Ideal
Description	Push-In Wire Connector, Gray Insulation Color, +221 °F Operating Temperature, 0.355 In Overall Length, 0.907 In Overall Width, 0.729 In Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture), 0.01 LB
Weight per unit	0.0098 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

connection	5 Ports
Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures
Wire Size	#12 AWG - #20 AWG Solid, #14 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand Or Less) Stranded, #12 AWG - #14 AWG (19 Strand Or Less) #16 AWG (26 Strand Or Less) 318 AWG (16 Strand Or Less) Stranded (Tin Bonded)
Wire Type	Solid, Stranded, Stranded (Tin Bonded)

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	0.355 IN Length X 0.907 IN Width X 0.729 IN Height
------	--

### Descriptions

Description	IN-SURE PUSH-IN WIRE CONN, 87 5-PRT GRAY, 150/JAR
Features	The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch circuit wiring application where a traditional twist-on wire connector would be used. Simply push the wire in – the low insertion force makes it easy.The color-coded shell allows for quick identification of port configuration while the clear polycarbonate housing allows for visual verification of every connection. The ergonomic design is easier to grip which me

### Manufacturer Information

Brand	Ideal
GTIN	00783250460779
UPC	783250460779

### Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Push-In



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Manufacturer Status	Inactive
minimum qty	150
Status	Inactive

## Packaging

Carton	150
Package	900
Weight Per each	0.0098

## Uses, Certifications, and Standards

standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS
Temperature Rating	105 DEG C Shell Rated