

E26 6" Trim Series


DESCRIPTION

Open trim with socket support in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- Open trim for BR30 and PAR30 lamps
- Torsion spring retention
- Socket support internal bracket



Dimensions:

A: 4-3/4"[122mm]
 H: 4-3/4"[122mm]
 OD: 7-1/4"[184mm]

Housings		Max Lamp Compatibility
H7ICT	H7ICAT	75W PAR30S, 75W PAR30L, 65W BR30
H7RICT	H7RICAT	65W BR30
E7ICAT	E7RICAT	300P: 75W PAR30S, 75W PAR30L, 65W BR30, 300SN, 300TBZ: 60W PAR30S, 60W PAR30L, 50W BR30
H7UICAT		75W PAR30S, 75W PAR30L, 85W BR30, 100W R30
H7ICTNB		75W PAR30S, 75W PAR30L, 65W BR30
H7ICATNB		75W PAR30S, 75W PAR30L, 65W PAR30, 300SN, 300TBZ: 60W PAR30S, 60W PAR30L, 50W BR30
E7ICATNB		75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
H7T		75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
E7TAT		75W PAR30S, 75W PAR30L, 65W BR30

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



300P
White Trim



300SN
Satin Nickel Trim



300TBZ
Tuscan Bronze Trim

300

6-Inch Open Trim with Socket Support

ORDERING INFORMATION

SAMPLE NUMBER: 300P

Trim	Finish
300P= 6" Haze Reflector, White Trim	WH=White
300SN= 6" Residential Gold Reflector, White Trim	WH=White
300TBZ= 6" Clear Specular Reflector, White Trim	WH=White

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
300P 300SN 300TBZ	Open	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		•	•	•	•	•	•		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•		•					
		H27RT	E27TAT	E27RTAT					

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



For use in Halo listed housings.



Select trims are classified for use in others housings. See www.eaton.com/lighting/legal.