




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30275 FLGD Ext Adapt 1/2IN 6 *Mulberry Metal*

Catalog Number	30275
Manufacturer	Mulberry Metal
Description	Mulberry; Box Extension; Flanged Style Take Off; Number Of Outlet: 6; Material: Heavy Duty Die Cast Aluminum; Cubic Capacity: 10 Cu-In; Includes: 2 Close-Up Plugs, Gaskets, and Mounting Screws; Outlet: 1/2 In, (2) Each End and (1) Each Side; Finish: Powder Coated
Weight per unit	N/A
Product Category	Bar Hangers & Outlet Box Accy.

Features

Material	Heavy Duty Die Cast Aluminum
number of outlet	6

Descriptions

Description	FLGD EXT ADAPT 1/2IN 6
extra long description	MULB 30275 FLANGED TAKE OFF 6H-1/2"
Long Description	Mulberry; Box Extension; Flanged Style Take Off; Number Of Outlet: 6; Material: Heavy Duty Die Cast Aluminum; Cubic Capacity: 10 CU-IN; Includes: 2 Close-Up Plugs, Gaskets, And Mounting Screws; Outlet: 1/2 IN, (2) Each End And (1) Each Side; Finish: Powder Coated
Product Type	Flanged Take Off 6H-1/2"
Special Features	Features: Provide An Additional 10 Cubic Inches; Allow Take-Off In Up To Four Directions For Lighting, Outlets, Or Switches; Heavy Duty Die-Cast Aluminum With Powder Finish; 2 Close-Up Plugs, Gaskets, And Mounting Screws Included; UL Listed And CSA Approved; Includes: 2 Close-Up Plugs, Gaskets, And Mounting Screws; Outlet: 1/2 IN, (2) Each End And (1) Each Side; Finish: Powder Coated

Manufacturer Information

Brand	Mulberry
GTIN	00095327302753
Manufacturers Part Number	30275
UPC	095327302753

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Flanged Style Take Off



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Application	For Wet Locations
standard	UL Listed, CSA Certified