



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1201 West Broadway  
79714-0000, TX Andrews  
Phone: 432-523-2423  
Fax: 432-523-2428



## 30410 Steel Crimp Connector, 410 18-10 Awg, 100/Bag

*Ideal*

Catalog Number	30410
Manufacturer	Ideal
Description	Ideal, Crimp Connector, Conductor Range: 1/14 Awg With 1/18 Awg Min, 2/10 Awg With 2/14 Awg Max, Finish: Zinc-Plated, Material: Steel, Copper Sleeves, Voltage Rating: 600 V, Model Number: 410, Model: 410
Weight per unit	0.0020 (lbs/each)
Product Category	Coaxial & Twinaxial Connectors

### Features

Material	Steel, Copper Sleeves
Voltage Rating	600

### Material, Color, and Finish

Finish	Zinc-plated
--------	-------------

### Descriptions

Description	STEEL CRIMP CONNECTOR, 410 18-10 AWG, 100/BAG
extra long description	IDEAL 30-410 CRIMP SLEEVE CONN 410
Features	Crimp connectors from IDEAL are designed for making fast, permanent, pressure-type connections. Whether there is a connection in a high vibration environment or installations at an OEM, there is a solution available. The steel and copper crimp connectors cover a wide range of combinations and have available insulating caps to protect against dangerous electrical shock.
Long Description	IDEAL, Crimp Connector, Conductor Range: 1/14 AWG With 1/18 AWG Min, 2/10 AWG With 2/14 AWG Max, Finish: Zinc-plated, Material: Steel, Copper Sleeves, Voltage Rating: 600 V, Model Number: 410, Model: 410
Product Type	Crimp Sleeve Conn 410 Bag 100
Special Features	Features: Minimum 1 #14 w/ 1 #18, Maximum 2 #10 w/ 2 #14; Rated For 600V Maximum; Designed For Fast, Permanent, Pressure-Type Connections; UL Listed And CSA Certified; Zinc-Plated Or Copper Sleeves Resist Corrosion; Will Not Vibrate Loose When Securely Crimped; UL Listed To 486C And CSA Certified To C22.2 #188; Comply With Federal Specification W-S-610E; Model Number: 410; Model: 410



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1201 West Broadway  
79714-0000, TX Andrews  
Phone: 432-523-2423  
Fax: 432-523-2428

## Manufacturer Information

Brand	Ideal
GTIN	00783250304103
Manufacturers Part Number	30-410
UPC	783250304103

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
Weight Per each	0.002

## Uses, Certifications, and Standards

Application	Designed For Fast, Permanent, Pressure-Type Connections, Long, Zinc-Plated Steel Sleeves Maximize Contact Area With Conductors, Will Not Vibrate Loose When Securely Crimped, UL Listed to 486C and CSA Certified to C22.2 #188, Comply With Federal Specifica
standard	CSA C22.2 #188, UL Listed to 486C, RoHS