



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30410 Steel Crimp Connector, 410 18-10 Awg, 100/Bag

Ideal

| | |
|------------------|---|
| Catalog Number | 30410 |
| Manufacturer | Ideal |
| Description | Ideal, Crimp Connector, Conductor Range: 1/14 Awg With 1/18 Awg Min, 2/10 Awg With 2/14 Awg Max, Finish: Zinc-Plated, Material: Steel, Copper Sleeves, Voltage Rating: 600 V, Model Number: 410, Model: 410 |
| Weight per unit | 0.0020 (lbs/each) |
| Product Category | Coaxial & Twinaxial Connectors |

Features

| | |
|----------------|-----------------------|
| Material | Steel, Copper Sleeves |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|--------|-------------|
| Finish | Zinc-plated |
|--------|-------------|

Descriptions

| | |
|------------------------|--|
| Description | STEEL CRIMP CONNECTOR, 410 18-10 AWG, 100/BAG |
| extra long description | IDEAL 30-410 CRIMP SLEEVE CONN 410 |
| Features | Crimp connectors from IDEAL are designed for making fast, permanent, pressure-type connections. Whether there is a connection in a high vibration environment or installations at an OEM, there is a solution available. The steel and copper crimp connectors cover a wide range of combinations and have available insulating caps to protect against dangerous electrical shock. |
| Long Description | IDEAL, Crimp Connector, Conductor Range: 1/14 AWG With 1/18 AWG Min, 2/10 AWG With 2/14 AWG Max, Finish: Zinc-plated, Material: Steel, Copper Sleeves, Voltage Rating: 600 V, Model Number: 410, Model: 410 |
| Product Type | Crimp Sleeve Conn 410 Bag 100 |
| Special Features | Features: Minimum 1 #14 w/ 1 #18, Maximum 2 #10 w/ 2 #14; Rated For 600V Maximum; Designed For Fast, Permanent, Pressure-Type Connections; UL Listed And CSA Certified; Zinc-Plated Or Copper Sleeves Resist Corrosion; Will Not Vibrate Loose When Securely Crimped; UL Listed To 486C And CSA Certified To C22.2 #188; Comply With Federal Specification W-S-610E; Model Number: 410; Model: 410 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250304103 |
| Manufacturers Part Number | 30-410 |
| UPC | 783250304103 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
|----------------------|--|

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Weight Per each | 0.002 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Designed For Fast, Perrmanent, Pressure-Type Connections, Long, Zinc-Plated Steel Sleeves Maximize Contact Area With Conductors, Will Not Vibrate Loose When Securely Crimped, UL Listed to 486C and CSA Certified to C22.2 #188, Comply With Federal Specifica |
| standard | CSA C22.2 #188, UL Listed to 486C, RoHS |