ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



30452 WING-NUT WIRE CONNECTOR, 452 RED, 100/BOX

IDEAL

Catalog Number	30452
Manufacturer	IDEAL
Description	Twist-On Wingnut, Red Insulation Color, +221 °F Operating Temperature, 1 to 6 Conductors, 600 V ac, 0.01 lb
Weight per unit	0.7100 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant polypropelene shell
Voltage Rating	600
Media	Yes

Material, Color, and Finish

Color	Red

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Description	WING-NUT WIRE CONNECTOR, 452 RED, 100/BOX
Features	Largest range in the Industry - from 2 #18 to up 4 #10High-leverage, contoured wing provides superior torque on every twistWide range, live-action spring handles small combinations and expands to accommodate large combinations as you need itCopolymer shell expands for smooth, progressive tightening providing dependable connectionsRemovable for repeat usage on same size or larger combinationsMore power with every twist.The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of
Long Description	IDEAL, Wire Connector, Wing-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Conductor Range: 18 - 8 AWG, Min 2 - 18, MAX 4-10, Material: Flame-retardant polypropelene shell, Color: Red, Voltage Rating: 600 V, Model Number: 452, Width: 1-15/64 IN, Height: 15/16 IN, Flammability Rating: UL 94V-2
Product Type	Wingnut 452 Red, 100 Box
Special Features	Comply With Federal Specification W-S-610E;Deep skirt helps protect against flash-over and turned-back strands for maximum dielectric protection;Features: Specially designed contour wings provide a secure grip for extra levarage;Flammability Rating: UL 94V-2;Height: 15/16 IN;Live action Spring expands to accept wire shape abd size with no pre-twisting required;Model Number: 452;Square wire spring threads directly onto conductors for fast, secure connections;Togh UL 94V-2 flame-retardent shell rated at 105
Extra Long Description	IDEAL 30-452 WINGNUT 452 RED, 100 B

Manufacturer Information

Brand	Ideal
	Ideal Industries
GTIN	00783250304523
UPC	783250

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Twist-On

Availability

Minimum Qty	100

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	100
Package	1000
Weight Per Each	0.7100 (lbs/each)

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
Environmental Conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
Standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E, RoHS Compliant