ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5617 Andrews Hwy
79762-0000, TX Odessa
Phone: 432-366-0008
Fax: 432-366-6045



30410 Steel Crimp Connector, 410 18-10 Awg, 100/Bag

Ideal

Catalog Number	30410
Manufacturer	Ideal
Description	Ideal, Crimp Connecter, Conductor Range: 1/14 Awg With 1/18 Awg Min, 2/10 Awg With 2/14 Awg Max, Finish: Zinc-Plated, Material: Steel, Copper Sleeves, Voltage Rating: 600 V, Model Number: 410, Model: 410
Weight per unit	0.2200 (lbs/each)
Product Category	Coaxial & Twinaxial Connectors

Features

Material	Steel, Copper Sleeves
Voltage Rating	600

Material, Color, and Finish

Finish	Zinc-plated

Descriptions

Description	STEEL CRIMP CONNECTOR, 410 18-10 AWG, 100/BAG
extra long description	IDEAL 30-410 CRIMP SLEEVE CONN 410
Features	Crimp connectors from IDEAL are designed for making fast, permanent, pressure-type connections. Whether there is a connection in a high vibration environment or installations at an OEM, there is a solution available. The steel and copper crimp connectors cover a wide range of combinations and have available insulating caps to protect against dangerous electrical shock.
Long Description	IDEAL, Crimp Connecter, Conductor Range: 1/14 AWG With 1/18 AWG Min, 2/10 AWG With 2/14 AWG Max, Finish: Zinc-plated, Material: Steel, Copper Sleeves, Voltage Rating: 600 V, Model Number: 410, Model: 410
Product Type	Crimp Sleeve Conn 410 Bag 100
Special Features	Features: Minimum 1 #14 w/ 1 #18, Maximum 2 #10 w/ 2 #14; Rated For 600V Maximum; Designed For Fast, Permanent, Pressure-Type Connections; UL Listed And CSA Certified; Zinc-Plated Or Copper Sleeves Resist Corrosion; Will Not Vibrate Loose When Securely Crimped; UL Listed To 486C And CSA Certified To C22.2 #188; Comply With Federal Specification W-S-610E; Model Number: 410; Model: 410

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5617 Andrews Hwy
79762-0000, TX Odessa
Phone: 432-366-0008
Fax: 432-366-6045

Manufacturer Information

Brand	Ideal
GTIN	00783250304103
Manufacturers Part Number	30-410
UPC	783250304103

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories

Availability

minimum qty	100

Packaging

Carton	100
Weight Per each	0.22

Uses, Certifications, and Standards

Application	Designed For Fast, Perrmanent, Pressure-Type Connections, Long, Zinc-Plated Steel Sleeves Maximize Contact Area With Conductors, Will Not Vibrate Loose When Securely Crimped, UL Listed to 486C and CSA Certified to C22.2 #188, Comply With Federal Specifica
standard	CSA C22.2 #188, UL Listed to 486C, RoHS