

"F" COAX CONNECTORS (Cont.)



"F" Male 1-Piece 1/8" Crimp-Attached

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
32-3000	32-3000-BU		1	Male Crimp-on with Attached 1/8" Crimp, 2 Pack	416 & 417	RG-59 & RG-62

"F" Male 1-Piece 1/8" Crimp-Gold Attached

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
32-3701	32-3701-BU		1	Male Crimp with Attached 1/8" Crimp-Gold	416	RG-59 & RG-62

"F" Male 1-Piece 1/4" Crimp-Attached

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
	32-412-BU		1	Male Crimp-on with Attached 1/4" Crimp-Ring	417	RG-6

"F" Male Twist-on Crimpless

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
	SD-447-BU		2	"F" Male Twist-on Connector, Crimpless	417	RG-6 Quad Shield
32-3002	32-3002-BU		3	"F" Male Twist-on Connector, Crimpless, 5 Pack	416	RG-59 & RG-62
32-3003	32-3003-BU		3	"F" Male Twist-on Connector, Crimpless, 5 Pack	417	RG-6

"F" Male Twist-on Crimpless-Gold

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
32-3702	32-3702-BU		3	"F" Male Twist-on Connector, Crimpless-Gold, 5 Pack	416	RG-59 & RG-62

"F" Male Twist-on with Quick-lock

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
	SD-448-BU		4	"F" Male Twist-on Quick-lock Connector	417	RG-6

"F" Male Twist-on Push-on

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
32-3202	32-3202-BU		5	"F" Male Twist-on Push-on Connector, 5 Pack	416	RG-59 & RG-62

"F" Male Gel-filled 1/8" Blue Connector with Sealer Ring

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
	SD-443-BU		6	"F" Male Gel-filled 1/8" Blue Connector with 1/4" Sealer Ring	417	RG-6
	SD-444-BU		7	"F" Male Gel-filled Connector with "O" Ring, Weatherproof Brass	417	RG-6

"F" Male Gel-filled Crimp with Permanent Crimp "O" Ring,-Nickel

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
32-445			8	"F" Male Crimp with Permanent Crimp "O" Ring,-Nickel, 2 Pack	417	RG-6
SD-445	SD-445-BU		8	"F" Male Crimp with Permanent Crimp "O" Ring,-Nickel, 2 Pack	417	RG-6

"F" Male 2-Piece Permanent Compression

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page(s)	Cable Type
	SD-446-BU		9	"F" Male 2-Piece Permanent Compression, Commercial, Weatherproof	417	RG-6

"F" Male Compression Locking Nut Only

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use With
	SD-446-1BU		10	"F" Male Compression Locking Nut Only, Weatherproof	Any female "F" type connector