

XT COBALT STEP BITS

MAXIMUM LIFE IN STAINLESS STEEL



XT **COBALT**
for Stainless Steel

FAST

New split point tip penetrates 10GA stainless steel in 10 seconds

INNOVATIVE

Dual-flute design makes for faster drilling with less force

DURABLE

Cobalt High Speed Steel maximizes heat and abrasion resistance



MADE FOR THE TRADE!™



DUAL-FLUTE

Two cutting edges share the load resulting in faster drill times with less force



COBALT HSS

Engineered for maximum life on stainless steel



30008C



34403C



34401C

STEAM OXIDE FINISH

Runs cooler and extends the life of the bit

NEW SPLIT POINT TIP

Eliminates walking and penetrates quickly

CUTS CLEAN, SMOOTH HOLES

SPECIFICATIONS

Stainless Steel Capacity Up to 10GA

Accessories Greenlee 462 Series Cutting Oil

Also cuts mild steel, copper, brass, aluminum, fiberglass, plastic, wood and laminates

CAT. NO.	# STEPS	MIN DIAMETER	INCREMENTS	MAX DIAMETER	HEX SHANK
34401C	13	1/8"	1/32"	1/2"	3/8"
34403C	12	3/16"	1/16"	7/8"	3/8"
30008C	3	1/2"	-	1-1/8"	3/8"
35884C	Includes all 3 step bit sizes in a case				

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
34401C	05789	XT Cobalt Step Bit, 1/2"
34403C	05790	XT Cobalt Step Bit, 7/8"
30008C	05792	XT Cobalt Step Bit, 1-1/8"
35884C	05793	XT Cobalt Step Bit, 1/2", 7/8", 1-1/8"



XT COBALT STEP BITS

MAXIMUM LIFE IN STAINLESS STEEL



XT COBALT
for Stainless Steel

FAST

New split point tip penetrates 10GA stainless steel in 10 seconds

INNOVATIVE

Dual-flute design makes for faster drilling with less force

DURABLE

Cobalt High Speed Steel maximizes heat and abrasion resistance



MADE FOR THE TRADE!™



COBALT HSS
Engineered for maximum life on stainless steel



DUAL-FLUTE
Two cutting edges share the load resulting in faster drill times with less force



STEAM OXIDE FINISH
Runs cooler and extends the life of the bit

NEW SPLIT POINT TIP
Eliminates walking and penetrates quickly

CUTS CLEAN, SMOOTH HOLES

SPECIFICATIONS

Stainless Steel Capacity Up to 10GA
Accessories Greenlee 462 Series Cutting Oil
Also cuts mild steel, copper, brass, aluminum, fiberglass, plastic, wood and laminates

CAT. NO.	# STEPS	MIN DIAMETER	INCREMENTS	MAX DIAMETER	HEX SHANK
34401C	13	1/8"	1/32"	1/2"	3/8"
34403C	12	3/16"	1/16"	7/8"	3/8"
30008C	3	1/2"	-	1-1/8"	3/8"
35884C	Includes all 3 step bit sizes in a case				

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
34401C	05789	XT Cobalt Step Bit, 1/2"
34403C	05790	XT Cobalt Step Bit, 7/8"
30008C	05792	XT Cobalt Step Bit, 1-1/8"
35884C	05793	XT Cobalt Step Bit, 1/2", 7/8", 1-1/8"

