



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3368143 600V 3P+G DS60 Inlet *Meltric Corporation*

Catalog Number	3368143
Manufacturer	Meltric Corporation
Description	Meltric 33-68143 Inlet, Enclosure Nema 3R, IP54/IP55, Wiring Capacity 10 to 2 Awg, Horsepower Rating 25 HP At 600 V 3 Phase, Polarity 3 Pole, Ground, Short Circuit Rating 100 Kamp, Application: Metals, Quarry, Automotive and Mining Industries, Standard: UI, Csa, Nom, IEC
Weight per unit	0.9700 (lbs/each)
Product Category	Pin & Sleeve Devices

### Features

amperage rating	60 Hz
Material	Polyester
Voltage Rating	600 VAC

### Material, Color, and Finish

Color	Blue Light
-------	------------

### Dimensions and Weight

Size	3.62 DIA X 2.20 IN
------	--------------------

### Descriptions

Description	600V 3P+G DS60 INLET
extra long description	MEL 33-68143 DS60 INLET
Long Description	Meltric 33-68143 Inlet, Enclosure NEMA 3R, IP54/IP55, Wiring Capacity 10 To 2 AWG, Horsepower Rating 25 HP At 600 V 3 Phase, Polarity 3 Pole, Ground, Short Circuit Rating 100 KAMP, Application: Metals, Quarry, Automotive and Mining Industries, Standard: UL, CSA, NOM, IEC
Product Type	DS60 Inlet
Special Features	Enclosure NEMA 3R, IP54/IP55, Wiring Capacity 10 To 2 AWG, Horsepower Rating 25 HP At 600 V 3 Phase, Polarity 3 Pole, Ground, Short Circuit Rating 100 KAMP

### Manufacturer Information

Brand	Meltric
GTIN	00784474123426
Manufacturers Part Number	33-68143
sub brand	Decontactor
UPC	784474123426



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	TRIP UNIT, INSULATED CASE TYPE; CSA APPROVAL; 800 AMPERE CURRENT RATING; INSTANTANEOUS/LONG DELAY TIME/SHORT DELAY TIME, GROUND FAULT DEFEATABLE ADJUSTMENT; MICROVERSATRIP[R] BRAND; REPLACEMENT TRIP UNIT; INCLUDES PROTECTIVE RELAY AND COMMUNICATION

## Packaging

Carton	1
Weight Per each	0.97

## Uses, Certifications, and Standards

Application	Metals, Quarry, Automotive and Mining Industries
standard	UL, CSA, NOM, IEC, CE, NFPA 70E
Temperature Rating	-40 to 140 F