



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 350T2 350 Al/Cu 2 Cond Stacked 2 Hole Lug

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | 350T2  |
| Manufacturer     | Nsi Industries   |
| Description      | 2 Port Stacked Lug 350 MCM - 6 Awg Stacked Lugs Are Large Size Set Screw Connectors With Wire Holes Stacked On Top Of Each Other to Minimize The Width Of The Connector. Made Of 6061T-6 Aluminum Alloy. Tin Plated For Low Contact Resistance. Suitable For Use With Both Copper and Aluminum Conductors. Rated 600 Volts (2000V Max. Per UL486B). UL486A/B Listed. Temperature Rating 90 Degrees C. Mounting Hole Spacing Is Nema Standard Of 1.75". |
| Weight per unit  | 0.2900 (lbs/each)  |
| Product Category | Large Terminals & Connectors   |

### Features

|          |        |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 350 AL/CU 2 COND STACKED 2 HOLE LUG  |
| extra long description | NSI 350T-2 Nema Panel Lug (3)600-2   |
| Features               | 2 Port Stacked Lug 350 MCM - 6 AWG Stacked Lugs are large size set screw connectors with wire holes stacked on top of each other to minimize the width of the connector. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts (2000V max. per UL486B). UL486A/B Listed. Temperature rating 90 degrees C. Mounting hole spacing is NEMA standard of 1.75". |

|                  |  |
|------------------|--|
| Long Description | 2 Port Stacked Lug 350 MCM - 6 AWG Stacked Lugs are large size set screw connectors with wire holes stacked on top of each other to minimize the width of the connector. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts (2000V max. per UL486B). UL486A/B Listed. Temperature rating 90 degrees C. Mounting hole spacing is NEMA standard of 1.75". |
|------------------|--|

|              |                                 |
|--------------|---------------------------------|
| Product Type | Nema Panel Lug (3)600-2 (24 Ea) |
|--------------|---------------------------------|

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381001818 |
| Manufacturers Part Number | 350T-2         |
| UPC                       | 662381001818   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS .....

### Packaging

Carton ..... 1 .....

Package ..... 10 .....

Weight Per each ..... 0.29 .....